

Eaton SPX200A0-5A2N1

Catalog Number: SPX200A0-5A2N1

Eaton SPX9000 adjustable frequency drive, Adjustable Frequency Drive, 200HP, NEMA Type 1/IP21, 575V, Three-phase, EMC N, FR10



Photo is representative

General specifications

Product Name	Catalog Number
Eaton SPX9000 adjustable frequency drive	SPX200A0-5A2N1
	UPC
	782116198559
Product Length/Depth	Product Height
23.7 in	79.45 in
Product Width	Product Weight
23.43 in	875 lb
Warranty	Certifications
2 year	IEC 61800-2
	UL 508C
	UL Listed
	EN 61800-3 Level H

defaultTaxonomyAttributeLabel

Brake chopper

No brake chopper

Modification

Standard boards

Frame size

FR10

Horsepower

200 hp

Software

Standard Software

Voltage rating

575 V

Rating

NEMA 1, IP21

Keypad

Alphanumeric

Input

Three-phase

EMC N

Resources

Application notes

Connecting drives to generator supplies

Electromagnetic compatibility (EMC)

SPI - Variable frequency drives with a common DC bus

Brochures

Variable frequency drive - Product overview

Catalogs

Eaton's Volume 6—Solid-State Motor Control

Product Range Catalog Drives Engineering

Product Datasheet - SPX200A0-5A2N1

Drawings

SPX_(FR10) 2D PDF

SPX_(FR10) 3D Model Xchange

SPX_(FR10) 2D Drawing Xchange

SPX_(FR10) 3D Inventor

SVX and SPX Series FR4-FR11 PDF Open Drawings

SPX_(FR10) AutoCAD 2D Footprint (mm)

SPX_(FR10) AutoCAD 2D Footprint

Multimedia

Eaton variable frequency drives - Demand more than good enough

Eaton variable frequency drives - Demand more innovation

Eaton variable frequency drives - Demand more expertise

How does a VFD work to save energy and money?

Specifications and datasheets

Eaton Specification Sheet - SPX200A0-5A2N1