

WSLMS48-CCT

High Power Linear Strip Light



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

WIRING:	Hardwire only. Installs easily to ceiling or wall. It may also be installed over a junction box using a canopy plate for an octagonal junction box. (NDR model: CVR500) Manufactured as a two-part unit; easily removed front panel and a wire back housing to allow for ease of installation.
HOUSING DETAILS:	The housing is formed steel with multiple 1/2" knockout locations for ease of installation. The motion sensor is a PIR sensor with a detection range of 13'(4m) to 19'(6m) and a time delay of 3 minutes. There are 4 functions of the PIR sensor that are controlled directly on the driver in the housing. 4 functions are: -ON: Default setting, light will turn off after 3 minutes of no movement -50%: Light will dim to 50% after 3 minutes of no movement -30%: Light will dim to 25% after 3 minutes of no movement -OFF: PIR motion sensor turned off, light ON/OFF controlled by light switch
OPTICS:	Offered with an acrylic frosted diffuser lens and LED strip technology to distribute light and optimize delivered high level of lumens.
ELECTRICAL:	Easily connected to a 120-277V power supply via provided UL recognized driver. 0-10V dimmable DAMP LOCATIONS rated Certifications: This product is ETL and DLC 5.1 listed in USA and Canada.
LENS:	The Python High Power Strip light has a frosted diffuser providing a uniform and widespread illumination.

COLOR TEMPERATURE:	3K - 35K -4K selectable
CRI:	80+
LUMEN OUTPUT:	3120 / 4200 / 5175 lumens
DIMMABLE:	Yes
WATTS:	26W / 35W / 45W selectable
LED LIFE:	50,000 hours
WARRANTY:	5 years
VOLTAGE:	120-277V
HEIGHT:	2.44" (6.2 cm)
LENGTH:	46.26" (117.6 cm)
WIDTH:	2.71" (6.9 cm)
INTEGRATED MOTION SENSOR:	Yes
MOTION SENSOR DETECTION RANGE:	13' - 19' (4m - 9m)

APPLICATIONS

The high power strip light equipped with the PIR motion sensor is ideal for many applications including corridors, stairwells, storage rooms, garages, laundry rooms and many other applications alike.

DIMENSIONS



ACCESSORIES



5" JUNCTION BOX COVER PLATE

This j-box cover has been designed to work with the viper series of products. it will protect an existing electrical j-box to prevent unsightly installation and potential damage. once installed, the j-box cover plate offers a clean and neat appearance for the light unit. fits to cover standard octagon junction box. painted white finish with 2 painted white screws included. 1/2" centre knockout hole for easy wiring and installation.

RATINGS



ORDERING GUIDE

PYTHON STRIP LIGHT SERIES

Series	Length	Color Temperature	Finish
WSLMS	48	CCT 3000K-3500K-4000K	WH White

Notes: Configure product using **BOLD** options: Ex: **WSLMS48-CCT-WH**