


# SDC

## COMMERCIAL AIR CURTAIN



### BIG ON COMFORT, BIG ON LOOKS!

Installed above sliding windows, the SDC's "air curtain" is the perfect solution for restaurant drive-throughs across Canada. The SDC puts instant heating control at your fingertips! It's ideal for commercial buildings and restaurant lobbies, and it's particularly suited for the special heating requirements of hospitals and schools. High-intensity heating capacity, even air flow and overall efficiency are its hallmarks, with an output of 1500 LFM powered by 5000 W. It's a heating powerhouse!

- **PERFECT FOR RESTAURANT DRIVE-THROUGHS**
- **"AIR CURTAIN" PREVENTS INTRODUCTION OF COLD AIR**
- **HIGH-CAPACITY (1500 LFM) YET SMALL**
- **EASY MAINTENANCE**
- **EASILY ACCESSIBLE CONTROLS**

#### COLOURS

- **standard:** white, soft white
- **Orora (optional):** refer to [www.stelpro.com/en-CA/Orora](http://www.stelpro.com/en-CA/Orora)

#### FINISH

- epoxy-polyester powdercoat

#### MANUFACTURING

- 18-gauge steel cabinet
- easy access to all components and easy maintenance via the front cover
- centrifugal fan
- thermal protection with automatic reset

#### ELEMENT

- nichrome element producing instant heat

#### CONTROL

- high/low switch
- on/off switch
- fan/heat or fan only switch
- 24V circuit (included with the C24 series) can be used with an external low voltage door contact (not provided)
- built-in thermostat (included with CT series)

#### INSTALLATION

- wall mounted (mounting bracket included)
- suspended with four 3/8 in. (9.5 mm) threaded rods (not provided)

#### WARRANTY

- three years



Periodic maintenance of air vents is highly recommended to ensure the maximum performance of the device.

#### IDEAL FOR:

restaurant drive-through, lobby, hospital, commercial space

# °STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. **No returns accepted on optional-colour products.** For all the latest models and prices, please refer to our website at [www.stelpro.com](http://www.stelpro.com).



# TECHNICAL SPECIFICATIONS

BUILT-IN THERMOSTAT		240 V CONTROL		24 V CONTROL		POWER HIGH/LOW	VOLTAGE	PHASE	LENGTH		WEIGHT		AIR SPEED
CODE	PRICE	CODE	PRICE	CODE	PRICE	WATTS	VOLTS	NB	MM	IN.	KG	LB	LFM
SDC0581CT	3 590.00	SDC0581C	3 414.00	SDC0581C24	3 414.00	5000/2500	208	1	613	24 1/8	23.6	52	1500
SDC0583CT	3 590.00	SDC0583C	3 414.00	SDC0583C24	3 414.00	5000/2500	208	3	613	24 1/8	23.6	52	1500
SDC0521CT	3 590.00	SDC0521C	3 414.00	SDC0521C24	3 414.00	5000/2500	240	1	613	24 1/8	23.6	52	1500
SDC0531CT	3 590.00	SDC0531C	3 414.00	SDC0531C24	3 414.00	5000/2500	347	1	613	24 1/8	23.6	52	1500
SDC0561CT	3 590.00	SDC0561C	3 414.00	SDC0561C24	3 414.00	5000/2500	600	1	613	24 1/8	23.6	52	1500
SDC0563CT	3 590.00	SDC0563C	3 414.00	SDC0563C24	3 414.00	5000/2500	600	3	613	24 1/8	23.6	52	1500

Add W for white or SW for soft white (consult the optional colours chart or contact your Stelpro representative for all other colours).  
Models also available in 277 V and 480 V.

# THROW DISTANCE AND HEAT RISE

UNITS	THROW DISTANCE		HEAT RISE	
KW	M	FT	°C	°F
5	12.2	40	6	11



# TECHNICAL DRAWINGS

