

# Eaton SVX020A1-4A1B1

Catalog Number: SVX020A1-4A1B1

Eaton SVX adjustable frequency drive, 20HP, NEMA Type 1/IP21, 480V, FR6, Three-phase, EMC H, Standard Software, A/N keypad, Internal brake chopper, Standard boards



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX020A1-4A1B1
<b>UPC</b>	<b>Product Length/Depth</b>
782116011513	9.3 in
<b>Product Height</b>	<b>Product Width</b>
22 in	7.6 in
<b>Product Weight</b>	<b>Warranty</b>
40.8 lb	2 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	EN 61800-3 Level H
	UL 508C
	IEC 61800-2

**Brake chopper**

Brake chopper

**Modification**

Standard boards

**Horsepower**

20 hp

**Frame size**

6

**Keypad**

Alphanumeric

**Input**

Three-phase

EMC H

**Rating**

NEMA 1, IP21

**Software**

Standard

**Application notes**[SPI - Variable frequency drives with a common DC bus](#)[Connecting drives to generator supplies](#)[Electromagnetic compatibility \(EMC\)](#)**Brochures**[SVX9000 Adjustable Frequency Drives Brochure](#)[SVX9000 Adjustable Frequency Drives Product Aid](#)**Catalogs**[Eaton's Volume 6—Solid-State Motor Control](#)[Product Range Catalog Drives Engineering](#)[Product Datasheet - SVX020A1-4A1B1](#)**Drawings**[SVX\\_\(FR6\) AutoCAD 2D Footprint](#)[SVX\\_\(FR6\) 2D PDF](#)[SVX\\_\(FR6\) 3D Model Xchange](#)[SVX\\_\(FR6\) 2D Drawing Xchange](#)[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)[SVX\\_\(FR6\) AutoCAD 2D Footprint \(mm\)](#)[SVX\\_\(FR6\) 3D Inventor](#)**Installation instructions**[9000X AFD User Manual](#)**Specifications and datasheets**[Eaton Specification Sheet - SVX020A1-4A1B1](#)