

circular conduc. terminal TA1.2 35...185 mm<sup>2</sup> 3 units accessory for: 3VA12



Model		
product brand name	SENTRON	
product designation	Circular conductor terminal 1 cable 3 units	
accessories	Wire connector	
General technical data		
designation / of the terminal	TA1.2	
type of electrical connection / with control wire tap	No	
Connections according IEC		
connectable conductor cross-section		
<ul style="list-style-type: none"> <li>• for copper cable / stranded / minimum</li> <li>• for copper cable / stranded / maximum</li> <li>• for aluminum cable / stranded / minimum</li> <li>• for aluminum cable / stranded / maximum</li> </ul>	50 mm <sup>2</sup> 185 mm <sup>2</sup> 50 mm <sup>2</sup> 185 mm <sup>2</sup>	
stripped length	20 mm	
tightening torque / when using copper cables		
<ul style="list-style-type: none"> <li>• stranded</li> <li>• finely stranded</li> </ul>	50 - 185 mm <sup>2</sup> : 22.6 Nm 95 - 150 mm <sup>2</sup> : 22.6 Nm	
Connections according UL		
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C	
stripped length	0.8 in	
Certificates		
General Product Approval	EMV	Test Certificates



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

Marine / Shipping	other	Environment
-------------------	-------	-------------



[Miscellaneous](#)

[Confirmation](#)

[Miscellaneous](#)



[Environmental Confirmations](#)

**Environment**

[Environmental Confirmations](#)

## Further information

### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9253-0JB12>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9253-0JB12>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9253-0JB12](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9253-0JB12)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/19/2024 

