

# Eaton SVX025A1-4A1B1

Catalog Number: SVX025A1-4A1B1

Eaton SVX adjustable frequency drive, Independent Drives, 25 hp, NEMA Type 1/IP21, 480V, FR6, Three-phase, EMC H, Standard Software, A/N keypad, Internal brake chopper, Standard boards



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX025A1-4A1B1
<b>UPC</b>	<b>Product Length/Depth</b>
782116011520	9.3 in
<b>Product Height</b>	<b>Product Width</b>
11.7 in	7.6 in
<b>Product Weight</b>	<b>Warranty</b>
40.8 lb	2 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	UL 508C
	IEC 61800-2
	EN 61800-3 Level H

[Brake chopper](#)

Brake chopper

[Modification](#)

Standard boards

[Horsepower](#)

25 hp

[Frame size](#)

6

[Keypad](#)

Alphanumeric

[Input](#)

Three-phase

EMC H

[Rating](#)

NEMA 1, IP21

[Software](#)

Standard

[Application notes](#)

SPI - Variable frequency drives with a common DC bus

Connecting drives to generator supplies

Electromagnetic compatibility (EMC)

[Brochures](#)

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

[Catalogs](#)

Product Range Catalog Drives Engineering

Product Datasheet - SVX025A1-4A1B1

Eaton's Volume 6—Solid-State Motor Control

[Drawings](#)

SVX and SPX Series FR4-FR11 PDF Open Drawings

SVX\_(FR6) 2D Drawing Xchange

SVX\_(FR6) 3D Model Xchange

SVX\_(FR6) 2D PDF

SVX\_(FR6) AutoCAD 2D Footprint

SVX\_(FR6) AutoCAD 2D Footprint (mm)

SVX\_(FR6) 3D Inventor

[Installation instructions](#)

9000X AFD User Manual

[Specifications and datasheets](#)

Eaton Specification Sheet - SVX025A1-4A1B1