


Ordering Information



Turn-Tell® Label Cassettes **PATENTED**

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Innovative label design allows labels to rotate for visibility from any angle, and for repositioning on the wire/cable to align legends and improve aesthetics
- Labels can be easily installed on existing terminated wires and assemblies without disconnecting the wires/cables




Part Number	Description	Labels per Cassette	Printer Compatibility				Print-On Area Color	Width		Length		Min. Cable O.D.		Max. Cable O.D.		Wire/Cable Size Range	Std. Pkg. Qty.	Std. Ctn. Qty.			
			MP75	MP100	MP200	MP300		In.	mm	In.	mm	In.	mm	In.	mm						
R100X075V1M	MP Cassette, Turn-Tell Self-Lam Label, Vinyl, 1.0" W x .75" H, .25" Print On Area, Clear/White	175					Black on White	1.0	25.4	0.75	19.1	0.12	3.1	0.16	4.1	Cat. 6 28 AWG/ 18 – 14 AWG	1	5			
R100X125V1M	MP Cassette, Turn-Tell Self-Lam Label, Vinyl, 1.0" W x 1.25" H, .38" Print On Area, Clear/White	125											1.25	31.8	0.16	4.1			0.22	5.6	Cat. 3 UTP/12 – 10 AWG
R100X150V1M	MP Cassette, Turn-Tell Self-Lam Label, Vinyl, 1.0" W x 1.50" H, .50" Print On Area, Clear/White	100	N	N	N	Y							1.5	38.1	0.22	5.6			0.28	7.1	Cat. 5e UTP/ Cat. 6 UTP/ Cat. 6A UTP/
R100X225V1M	MP Cassette, Turn-Tell Self-Lam Label, Vinyl, 1.0" W x 2.25" H, .75" Print On Area, Clear/White	75											2.25	57.2	0.28	7.1			0.39	9.9	Cat. 6 FTP/Cat. 6 UTP/Cat. 6A FTP/8-4 AWG

Representative offering only, visit www.panduit.com for complete listing of products.



Continuous Self-Laminating Labels

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Self-laminating adhesive labels for wire/cable identification include a white print-on area and clear over-laminate



Part Number	Description	Printer Compatibility				Print-On Area Color	Width		Length		Print-On Area Width		Min. Cable O.D.		Max. Cable O.D.		Wire/Cable Size Range	Std. Pkg. Qty.	Std. Ctn. Qty.
		MP75	MP100	MP200	MP300		In.	mm	Ft.	m	In.	mm	In.	mm	In.	mm			
S000X100VAM	MP Cassette, Continuous Self-Lam Tape, Vinyl, 1.0" W x 26' L, White	N	Y	Y	Y	White	0.945	24	26.2	8.0	0.315	8	0.10	2.5	0.20	5.1	12 – 10 AWG	1	5
S000X150VAM	MP Cassette, Continuous Self-Lam Tape, Vinyl, 1.5" W x 26' L, White	N	N	N	Y	White	1.417	36	26.2	8.0	0.512	13.0	0.16	4.0	0.32	8.1	Cat. 5e/ Cat. 6	1	5


Representative offering only, visit www.panduit.com for complete listing of products.

Ordering Information



Marker Plate Label Cassettes

- Fast-loading PXE™ Label Cassette includes both label material and ribbon to make changing labels easy
- Non-adhesive and halogen free; used to identify wires, cables, equipment, and many other applications
- Designed for use on larger diameter wire/cables and may be applied after all terminations are complete
- Attachable in horizontal or vertical orientation.
- Meets requirements for MIL-STD-202G, Method 215K, Soutlion A, C and D
- Meets the outgassing requirements of ASTM E-595 suitable for use in air handling spaces.

 Polyester/Polyolefin (Y6, Y7)

 -40°F to 180°F (-40°C to 82°C)

Part Number	Description	Printer Compatibility				Print-On Area Color	Width		Length		Print-On Area Width		Recommended Cable Tie		Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
		MP75	MP100	MP200	MP300		In.	mm	In.	mm	In.	mm	Vertical	Horizontal			
M300X050Y6M	PXE Cassette, Marker plate, polyester, 3.0" W x .50" H, Yellow	N	N	N	Y	Black on Yellow	3.00	76.2	0.50	12.7	1.80	45.7	PLT2.5I-C	PLT2.5I-C	65	1	5
M300X050Y7M	PXE Cassette, Marker plate, polyester, 3.0" W x .50" H, White	N	N	N	Y	Black on White	3.00	76.2	0.50	12.7	1.80	45.7	PLT2.5I-C	PLT2.5I-C	65	1	5

Representative offering only, visit www.panduit.com for complete listing of products.



Like what you see and want more?


Visit www.panduit.com/mobileprinters for the full offering of Panduit products

Ordering Information



Non-Laminated Label Cassettes

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Non-laminated adhesive labels for wire/cable identification

 Nylon Cloth (C1M)

 -65°F to 275°F (-54°C to 135°C)

Die-Cut Nylon Cloth Labels

Part Number	Description	Printer Compatibility				Print-On Area Color	Width		Length		Min. Cable O.D.		Max. Wire O.D.		Wire Range	Labels Per Cassette	Std. Pkg. Qty.	Std. Ctn. Qty.
		MP75	MP100	MP200	MP300		In.	mm	In.	mm	In.	mm	In.	mm				
N050X075C1M	PXE Cassette, Comp Label, Adhesive Nylon Cloth, 0.50" W x .75" H, White	N	N	N	Y	Black on White	0.50	12.7	0.75	19.1	0.12	3.1	0.16	4.1	12 - 10 AWG	275	1	5
N100X075C1M	PXE Cassette, Comp Label, Adhesive Nylon Cloth, 1.00" W x .75" H, White						1.00	25.4										
N100X125C1M	PXE Cassette, Comp Label, Adhesive Nylon Cloth, 1.00" W x 1.25" H, White						1.25	31.8	0.2	5.1	0.32	8.1	10 - 6 AWG	180				

Continuous Nylon Cloth Tape

Part Number	Description	Printer Compatibility				Print-On Area Color	Height		Length		Std. Pkg. Qty.	Std. Ctn. Qty.
		MP75	MP100	MP200	MP300		In.	mm	Ft.	m		
T050X000C1M-BK	MP Cassette, Continuous Tape, Nylon Cloth, 0.50" W x 19' L, Black on White	Y	N	Y	Y	Black on White	0.465	11.82	19	6	1	5
T075X000C1M-BK	MP Cassette, Continuous Tape, Nylon Cloth, 0.75" W x 19' L, Black on White						0.702	17.82				
T100X000C1M-BK	MP Cassette, Continuous Tape, Nylon Cloth, 1.00" W x 19' L, Black on White						0.938	23.82				