



PRODUCT-DETAILS

# XT1H 125 TMF 125-1250 3p F F UL/CSA

## XT1H 125 TMF 125-1250 3p F F UL/CSA



General Information	
Extended Product Type	XT1H 125 TMF 125-1250 3p F F UL/CSA
Product ID	1SDA074708R1
EAN	8015644786854
Catalog Description	XT1H 125 TMF 125-1250 3p F F UL/CSA
Long Description	XT1H 125 TMF 125-1250 3p F F UL/CSA

ABB EcoSolutions	
ABB EcoSolutions	Yes

Circular Value	
Circular Design Principles Recyclability Rate	Design for Closing Resource Loops - Standard EN45555 - 55.9 %
End of Life Instructions Group Waste to Landfill	9AKK108468A2347 UL 2799 Zero Waste To Landfill Validation available

Target

### Eco Transparency

Environmental Product Declaration - EPD	9AKK108468A1890
---	-----------------

### Environmental

Environmental Information	9AKK108467A6707
---------------------------	-----------------

### Material Compliance

REACH Declaration	9AKK108466A1425
RoHS Information	9AKK108466A1424
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
Toxic Substances Control Act - TSCA	9AKK108467A8326

### Ordering

Order Code US and Canada	XT1HU3125AFF000XXX
EAN	8015644786854
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

### Dimensions

Product Net Width	76.2 mm
Product Net Height	130 mm
Product Net Depth / Length	70 mm
Product Net Weight	1.1 kg

### Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	128 mm
Package Level 1 Height	135 mm
Package Level 1 Depth / Length	143 mm
Package Level 1 Gross Weight	1.19 kg
Package Level 1 EAN	8015644786854

### Additional Information

Circuit Breaker Type to be Associated	Power Distribution
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	Automatic Circuit Breaker
Suitable for Product Class	SACE Tmax XT
Version	F
CAD Dimensional Drawing	1SDH001295R0008

## Technical

Connecting Capacity Main Circuit	Busbar 45.5 ... 80 mm <sup>2</sup>
Current Type	AC/DC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	240 cycles per hour 25000 cycle
Number of Poles	3
Opening Time	CB with SOR 15 ms CB with UVR 15 ms
Order Multiple	1 piece
Power Loss	at Rated Operating Conditions per Pole 10.7 W
Rated Current (I <sub>n</sub> )	125 A
Rated Instantaneous Short-Circuit Current Setting (I <sub>i</sub> )	1250 A
Rated Operational Voltage	600Y/347 V AC 500 V DC
Rated Uninterrupted Current (I <sub>u</sub> )	125 A
Rated Voltage (U <sub>r</sub> )	600Y/347 V
Recommended Screw Driver	Main Circuit M6
Release	TMF
Release Type	TM
Setting Range	125 A
Short-Circuit Performance Level	H
Standards	UL489
Sub-type	XT1
Terminal Connection Type	Front
Terminal Type	Bolt
Tightening Torque	6 N·m

## Technical UL/CSA

Interrupting Rating acc. to UL489	(240 V AC) 100 kA (480 V AC) 65 kA (600Y / 347 V AC) 25 kA (250 V DC) 2 Poles in Series 50 kA (500 V DC) 4 Poles in Series Kind 50 kA
-----------------------------------	---

---

## Certificates and Declarations

---

ATEX Certificate	No certification needed
CSA Certificate (Intrinsic Safe)	9AKK10103A3905
Data Sheet, Technical Information	2CDC210017C0101 1SDC210200D0206 1SDC210199D0206
Declaration of Conformity - CE	9AKK106713A5532
UL Certificate	1SDL000163R0111
VDE Certificate	No certification needed
Dimension Diagram	1SDH000719R0100
Mechanical Drawings	1SDH000719R0100
Wiring Diagram	1SDM000068R0001
Instructions and Manuals	1SDH000719R0003

---



---

## Classifications

---

ETIM 8	EC000228 - Power circuit-breaker for trafo/generator/installation protection
ETIM 9	EC000228 - Power circuit-breaker for trafo/generator/installation protection
IDEA Granular Category Code (IGCC)	4927 >> Molded case circuit breakers
Object Classification Code	Q
UNSPSC	39121616
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
eClass	V11.1 : 27370409

---



---

## Categories

---

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

