



LED PAR30 S/L

8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB



Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General Information		Temperature	
Cap-Base	E26 [Single Contact Medium Screw]	Warm-up time to 60% light	0.5 s
Nominal lifetime	25,000 hour(s)	Power Factor (Fraction)	0.7
Switching Cycle	50,000	Voltage (Nom)	120 V
Lighting Technology	LED	Temperature	
Light Technical		Ambient temperature range	-40 to +45 °C
Color Code	927 [CCT of 2700K]	T-Case Maximum (Nom)	85 °C
Beam Angle (Nom)	25 degree(s)	Controls and Dimming	
Luminous Flux	850 lm	Dimmable	Only with specific dimmers
Luminous Intensity (Nom)	3,300 cd	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	100 lm/W	Bulb Finish	Clear
Color Designation	Warm White (WW)	Bulb Material	Plastic
Correlated Color Temperature (Nom)	2700 K	Bulb Shape	PAR30S
Color Consistency	<4	UL Wet/ damp/ dry location	Wet location
Color rendering index (CRI)	90	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Suitable For Accent Lighting	Yes
Operating and Electrical		T20 compliant	Yes
Input Frequency	60 Hz	EU RoHS compliant	Yes
Power Consumption	8.5 W		
Lamp Current (Nom)	105 mA		
Wattage Equivalent	75 W		
Starting Time (Nom)	0.5 s		

LED PAR30 S/L

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 8.5PAR30S/COR/927/F25/D/P/ULW/T20
6/1FB

