



PRODUCT-DETAILS

XT4V 250 TMF 40-400 3p F F UL/CSA

XT4V 250 TMF 40-400 3p F F UL/CSA



General Information	
Extended Product Type	XT4V 250 TMF 40-400 3p F F UL/CSA
Product ID	1SDA075294R1
EAN	8015644792718
Catalog Description	XT4V 250 TMF 40-400 3p F F UL/CSA
Long Description	C.BREAKER TMAX XT4V 250 UL/CSA FIXED THREE-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMF R 40-400 A

ABB EcoSolutions	
ABB EcoSolutions	Yes

Circular Value	
Circular Design Principles Recyclability Rate	Design for Closing Resource Loops - Standard EN45555 - 56.30 %
End of Life Instructions	9AKK108468A2351
Group Waste to Landfill Target	UL 2799 Zero Waste To Landfill Validation available

---

### Eco Transparency

---

Environmental Product Declaration - EPD	9AKK108468A1892
---	-----------------

---



---

### Environmental

---

Environmental Information	9AKK108467A6707
---------------------------	-----------------

---



---

### Material Compliance

---

REACH Declaration	9AKK108466A1425
RoHS Information	9AKK108466A1424
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
Toxic Substances Control Act - TSCA	9AKK108467A8326

---



---

### Ordering

---

Order Code US and Canada	XT4VU3040AFF000XXX
EAN	8015644792718
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

---



---

### Dimensions

---

Product Net Width	105 mm
Product Net Height	160 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	2.5 kg

---



---

### Container Information

---

Package Level 1 Units	box 1 piece
Package Level 1 Width	145 mm
Package Level 1 Height	210 mm
Package Level 1 Depth / Length	168 mm
Package Level 1 Gross Weight	2.5 kg
Package Level 1 EAN	8015644792718

---



---

### Additional Information

---

Circuit Breaker Type to be Associated	Power Distribution
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	Automatic Circuit Breaker
Suitable for Product Class	SACE Tmax XT
Version	F

**Technical**

Connecting Capacity Main Circuit	Busbar 85..200 mm <sup>2</sup>
Current Type	AC/DC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	240 cycles per hour 25000 cycle
Number of Poles	3
Opening Time	CB with SOR 15 ms CB with UVR 15 ms
Order Multiple	1 piece
Power Loss	at Rated Operating Conditions per Pole 4.5 W
Rated Current (I <sub>n</sub> )	40 A
Rated Instantaneous Short-Circuit Current Setting (I <sub>s</sub> )	400 A
Rated Operational Voltage	600 V AC 600 V DC
Rated Uninterrupted Current (I <sub>u</sub> )	250 A
Rated Voltage (U <sub>r</sub> )	600 V
Recommended Screw Driver	Main Circuit M8
Release	TMF
Release Type	TM
Setting Range	40 A
Short-Circuit Performance Level	V
Standards	UL489
Sub-type	XT4
Terminal Connection Type	Front
Terminal Type	Bolt
Tightening Torque	8 N·m

**Technical UL/CSA**

Interrupting Rating acc. to UL489	(240 V AC) 200 kA (480 V AC) 150 kA (600 V AC) 65 kA (250 V DC) 2 Poles in Series 100 kA (600 V DC) 3 Poles in Series 85 kA
-----------------------------------	---

**Certificates and Declarations**

ATEX Certificate	No certification needed
CSA Certificate (Intrinsic Safe)	9AKK10103A3908
Data Sheet, Technical Information	1SDC210200D0206 1SDC210199D0206
Declaration of Conformity - CE	9AKK106713A5529
UL Certificate	1SDL000163R0114
VDE Certificate	No certification needed
Dimension Diagram	1SDH000722R0100
Mechanical Drawings	1SDH000722R0100
Wiring Diagram	1SDM000068R0001

---

## Classifications

---

ETIM 8	EC000228 - Power circuit-breaker for trafo/generator/installation protection
ETIM 9	EC000228 - Power circuit-breaker for trafo/generator/installation protection
IDEA Granular Category Code (IGCC)	4927 >> Molded case circuit breakers
Object Classification Code	Q
UNSPSC	39121616
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
eClass	V11.1 : 27370409

---

---

## Categories

---

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

