

# Compression Terminal

By Burndy  
Catalog # [YAL4CT516](#)

Copper HYLUG™, Single Hole w/ Inspection Window, 4 AWG, 5/16" Stud, 8 index, Grey, Short Barrel, Electro- Tin Plated.



## Application

Wire Termination

## General

Catalog Number	YAL4CT516
Color Code	Gray
Connector Type	STANDARD BARREL
Die Index	8
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810417546

## Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - D inch	0.83 in
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.79 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.51 in
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - CSD029213](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-YAL4CT516-SPEC-EN | REV 6/2024