

E-CLASS™ FISH TAPE

GLOW-IN-DARK EYELET | 1000V

NEW
PRODUCT



SCAN to see all IDEAL® Wire
Installation Products



E-CLASS™ FISH TAPE

GLOW-IN-DARK EYELET | 1000V

E-Class™ Fiberglass Fish Tapes are non-conductive up to 1000V* for use around existing circuits and feature a glow in the dark molded eyelet for greater visibility in dark areas. A fiberglass core provides column strength for good pushing and pulling capability, with a round jacket assisting in feeding through runs with multiple bends or in multiple planes. The E-Class™ Fiberglass Fish Tape is available in two lengths, 100 ft. and 200 ft.

Features:

- Non-conductive up to 1000V* designed for use around existing circuits
- E-Class™ fiberglass core for great strength and pushing power
- Glow in the Dark eyelet for greater visibility and ease of use in dark areas
- Smooth nylon jacket protects fiberglass and provides a smooth surface for navigating bends
- Round shape provides omni-directional pushing through tough bends
- 3/16" overall tape diameter with pulling strength of 350 lbs.



Glow-in-Dark Tip

Greater visibility for ease of use in dark areas.




Tuff-Grip™ Pro Handle

Durable case with full perimeter handle band that helps keep dirt & moisture out while withstanding multiple drops from 25' onto concrete.



Non-Conductive

Up to 1000V* for use around existing circuits



Length (ft.)	Case Diameter (in.)	Part No.
100	12	31-046
200	16	31-048

Description	Part No.
Repair Kit (includes two eyelets and adhesive)	31-044

Scan for Complete Fish Tape User Guide



IDEAL INDUSTRIES, INC.
1800 S. Prairie Drive, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA

International offices:
Australia • Canada • China • India • Mexico • UK

Form No. P-6080
©2024 IDEAL INDUSTRIES, INC.

3/24
Printed in U.S.A.

The Fish Tape square inlay with notched corner combined with an ergonomic handle is a registered trademark of IDEAL INDUSTRIES, INC. Registered United States Patent and Trademark Office.

The blue color of the Fish Tape products is a registered trademark of IDEAL INDUSTRIES, INC. Registered United States Patent and Trademark Office.

**Based on internal testing.*