




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- *1. REFER TO www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR
2. SPLICING MAY OCCUR FOR ROLL SIZES LONGER THAN 10 FT.
3. REVERSE CUT.
4. SOME GAP WILL BE PRESENT BETWEEN WINDS
5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS EUROPEAN DIRECTIVE ON THE RESTRICTION OF HAZARDOUS SUBSTANCES AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
6. DIMENSIONS IN [] ARE METRIC.

*PANDUIT PART NUMBER	A IN [mm]	B IN [mm]	T IN [mm]	WEIGHT LBS (g)/ 100 FT
T12F	.125 [3.2]	.218 ±.047 [5.5 ±1.2]	.030 ±.006 [0.8 ±0.2]	0.4 (200)
T19F	.188 [4.8]	.250 ±.047 [6.4 ±1.2]	.035 ±.008 [0.9 ±0.2]	0.7 (300)
T25F	.250 [6.4]	.375 ±.047 [9.5 ±1.2]	.040 ±.008 [1.0 ±0.2]	1.1 (500)
T38F	.375 [9.5]	.437 ±.047 [11.1 ±1.2]	.055 ±.010 [1.4 ±0.3]	2.2 (1000)
T50F	.500 [12.7]	.500 ±.047 [12.7 ±1.2]	.060 ±.016 [1.5 ±0.4]	3.3 (1500)
T62F	.625 [15.9]	.625 ±.047 [15.9 ±1.2]	.062 ±.020 [1.6 ±0.5]	4.4 (2000)
T75F	.750 [19.1]	.875 ±.047 [22.2 ±1.2]	.065 ±.020 [1.7 ±0.5]	5.6 (2550)
T100F	1.000 [25.4]	1.125 ±.047 [28.6 ±1.2]	.070 ±.020 [1.8 ±0.5]	8.2 (3750)



PART NUMBER					SEE TABLE																			
TITLE										POLYETHYLENE SPIRAL WRAP														
										CUSTOMER DRAWING														
ITEM REVISION NAME					03903NBB/00																			
DATASET FILE NAME					03903NBB_DC/00A																			
 THIRD ANGLE PROJECTION																								
MATERIAL										POLYETHYLENE					DRAWING NUMBER					03903NBB - DC				
REV	DATE	BY	CHK	APR	DESCRIPTION					ECN	DRAWN BY	DATE	CHK	SCALE	SHEET 1 OF 1					SIZE				
00A	06/19/2024	KLN	SEWH	MSAD	INITIAL RELEASE					GAECN07120/00	KLN	06/19/2024	MSAD	NONE						A				

A-SIZE CUSTOMER