

Infeed left Connection main circuit: screw terminal 3 slots for compact load feeders Connection terminal maximum 50 mm<sup>2</sup> / 70 mm<sup>2</sup>

General technical data		
product brand name		SIRIUS
product designation		infeed left
protection class IP on the front according to IEC 60529		IP20; IP20 with box terminal/cover
touch protection on the front according to IEC 60529		Finger-safe, for vertical contact
degree of pollution		3
number of slots for compact feeder		3
installation altitude at height above sea level maximum	m	2 000
ambient temperature		
• during transport	°C	-55 ... +80
• during storage	°C	-55 ... +80
• during operation	°C	-20 ... +60
vibration resistance		f = 4 to 5.8 Hz; d = 15 mm; f = 5.8 to 500 Hz; a = 2 m / s <sup>2</sup> 10 cycles
shock resistance		Semi-sinusoidal a = 6 m/s <sup>2</sup> at 10 ms; 3 pos. and 3 neg. Shock in all axes
reference code		
• according to IEC 81346-2		W
• according to EN 61346-2		W
Main circuit		
operational current at AC at 400 V rated value	A	100
operating voltage at AC-3 rated value maximum	V	690
Installation/ mounting/ dimensions		
fastening method		screw and snap-on mounting
width	mm	205
height	mm	197
depth	mm	155
Connections/ Terminals		
type of electrical connection for main current circuit		screw-type terminals
design of screw-type connection for main contacts		M3
stripped length for main contacts	mm	17
tightening torque for main contacts with screw-type terminals	N·m	6 ... 8
type of connectable conductor cross-sections for supply for main contacts using the upper clamping point		
• solid		2.5 ... 70 mm <sup>2</sup>
• stranded		2.5 ... 70 mm <sup>2</sup>
• finely stranded with core end processing		2.5 ... 35 mm <sup>2</sup>
• finely stranded without core end processing		4 ... 50 mm <sup>2</sup>
type of connectable conductor cross-sections for supply for main contacts using the lower clamping point		
• solid		2.5 ... 70 mm <sup>2</sup>

<ul style="list-style-type: none"> <li>• stranded</li> <li>• finely stranded with core end processing</li> <li>• finely stranded without core end processing</li> </ul>	2.5 ... 70 mm <sup>2</sup> 2.5 ... 50 mm <sup>2</sup> 10 ... 50 mm <sup>2</sup>
<b>type of connectable conductor cross-sections for supply for main contacts using both clamping points</b> <ul style="list-style-type: none"> <li>• solid</li> <li>• stranded</li> <li>• finely stranded with core end processing</li> <li>• finely stranded without core end processing</li> </ul>	2 x (2.5 ... 50 mm <sup>2</sup> ) 2 x (2.5 ... 50 mm <sup>2</sup> ) 2 x (2.5 ... 35 mm <sup>2</sup> ) 2 x (4 ... 35 mm <sup>2</sup> )
<b>type of connectable conductor cross-sections for AWG cables</b> <ul style="list-style-type: none"> <li>• for supply for main contacts using the upper clamping point</li> <li>• for supply for main contacts using the lower clamping point</li> <li>• for supply for main contacts using both clamping points</li> <li>• for main contacts for load-side outgoing feeder</li> </ul>	10 ... 2/0 10 ... 2/0 2 x (10 ... 1/0) 2 x (16 ... 10), 1 x (16 ... 8)

**Certificates/ approvals**

General Product Approval	EMV
--------------------------	-----



[Confirmation](#)



Test Certificates	Marine / Shipping	other	Environment
-------------------	-------------------	-------	-------------

[Type Test Certificates/Test Report](#)



[Confirmation](#)

[Environmental Confirmations](#)

**Further information**

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA6813-8AB>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA6813-8AB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA6813-8AB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RA6813-8AB&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA6813-8AB&lang=en)



last modified:

12/15/2020 