

# HELIX™ FISH TAPE

ULTRA FLEXIBLE | 1000V

**IDEAL**  
electrical™

SCAN TO SEE  
ALL IDEAL® WIRE  
INSTALLATION  
PRODUCTS



# HELIX™ FISH TAPE

## ULTRA FLEXIBLE | 1000V

Helix™ Fish Tapes utilize a triple strand braided construction making them highly flexible for short, complex runs. Featuring the molded eyelets, they are non-conductive up to 1000V\* for use around existing circuits. The Helix creates ridges on the exterior of the tape which reduces the amount of friction through the conduit.

Helix™ Fish Tapes are available in three lengths, 50, 100 and 200 feet

### Features:

- Triple strand braided design for ultra flexibility
- Non-conductive up to 1000V\* for use around existing circuits
- Tape construction creates a balance between column strength and flexibility
- Ridges on the exterior of the tape minimize friction in conduit
- Great for use on short, complex runs
- Pulling strength: 200 lb




### Ultra-Flexible

Ultra-flexible material for use in complex runs.



### Tuff-Grip™ Pro Handle

Durable case with full perimeter handle band that helps keep dirt & moisture out while withstanding multiple drops from 25' onto concrete.



### Non-Conductive

Up to 1000V\* for use around existing circuits

DESCRIPTION	PART #
Helix™ Fish Tape 50'	<b>31-075</b>
Helix™ Fish Tape 100'	<b>31-076</b>
Helix™ Fish Tape 200'	<b>31-077</b>

P-6082 (9-24)  
©IDEAL INDUSTRIES, INC.

The fish tape square inlay with notched corner combined with an ergonomic handle is a registered trademark of IDEAL INDUSTRIES, INC. Registered United States Patent and Trademark Office.

The blue color of the fish tape products is a registered trademark of IDEAL INDUSTRIES, INC. Registered United States Patent and Trademark Office.

\*Based on internal testing.

