

**2024 Specification Sheet - English**

---

**LONG DESCRIPTION –**

---

**Long Description Marketing Copy**

Precision-machined tips for exact fit. Handle marked for easy identification of screwdriver size, type and length. Strong, durable black phosphate tips prevent chipping of plating. Soft, cushioned grip for extra comfort and torque

**PRODUCT NAME –**

---

**Page Title**

Heavy-Duty Phillips Tip #2 x 10" Screwdriver

**PRODUCT OVERVIEW –**

---

**Marketing Text 1**

Precision-machined tips for exact fit

**Marketing Text 2**

Handle marked for easy identification of screwdriver size, type and length

**Marketing Text 3**

Strong, durable black phosphate tips prevent chipping of plating

**Marketing Text 4**

Soft, cushioned grip for extra comfort and torque

**Marketing Text 5**

Exceeds ASME/ANSI specifications

**Marketing Text 6**

Lifetime limited warranty

**Marketing Text 7**

Note: This is not an insulated tool

**PRODUCT SPECIFICATION –**

---

**Product Specification 1**

Finish : Black Phosphate Plated Tip

**Product Specification 2**

Handle Type : Soft, Cushioned Grip

**Product Specification 3**

Overall Length : 14-5/16 IN (36.400 CM)

**Product Specification 4**

Shank Length : 10.000 IN

**Product Specification 5**

Standard : ASME/ANSI

**Product Specification 6**

Tip Size : #2

**Product Specification 7**

Tip Type : Phillips

**Product Specification 8**

Type : Heavy Duty

**Product Specification 9**

Weight : 0.400 LB (0.180 KG)