

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Forged from chrome vanadium steel for greater durability and strength. Precision-machined and laser-hardened blades strengthen cutters and provide consistent performance. Effectively cuts most hardened wire, ACSR, bolts, screws and nails. Through-hardened steel for longer life

PRODUCT NAME –

Page Title

8" High-Leverage Diagonal Cutting Pliers, Angled Head (Dipped Grip)

PRODUCT OVERVIEW –

Marketing Text 1

Forged from chrome vanadium steel for greater durability and strength

Marketing Text 2

Precision-machined and laser-hardened blades strengthen cutters and provide consistent performance

Marketing Text 3

Effectively cuts most hardened wire, ACSR, bolts, screws and nails

Marketing Text 4

Through-hardened steel for longer life

Marketing Text 5

Dual cutting edges for optimum cutting performance

Marketing Text 6

Exceeds ASME/ANSI specifications

Marketing Text 7

Rugged riveted construction for smooth precise action

Marketing Text 8

Lifetime limited warranty

Marketing Text 9

Note: This is not an insulated tool

Marketing Text 10

Dipped Grip Only: Double layered vinyl handles for comfort and slip resistance

Marketing Text 11

Reduced handle size allows for easy storage of tools in pouches and tool bags

PRODUCT SPECIFICATION –

Product Specification 1

Application : For Cutting Most Hardened Wire, ACSR, Bolts, Screws And Nails

Product Specification 2

Handle Type : Dipped Grip, Double Layered Vinyl Handle

Product Specification 3

Material : Chrome Vanadium Steel

Product Specification 4

Overall Length : 8-3/4 IN (22.200 CM)

Product Specification 5

Size : 8.000 IN

Product Specification 6

Standard : ASME/ANSI

Product Specification 7

Type : High Leverage Diagonal

Product Specification 8

Weight : 0.850 LB (0.390 KG)