

2024 Specification Sheet - English

**LONG DESCRIPTION –**

Long Description Marketing Copy

Forged from chrome vanadium steel for greater durability and strength. Precision-machined and laser-hardened blades strengthen cutters and provide consistent performance. Effectively cuts most hardened wire, ACSR, bolts, screws and nails. Through-hardened steel for longer life

PRODUCT NAME –

Page Title

8" High-Leverage Diagonal Cutting Pliers, Angled Head (Molded Grip)

PRODUCT OVERVIEW –

Marketing Text 1

Forged from chrome vanadium steel for greater durability and strength

Marketing Text 2

Precision-machined and laser-hardened blades strengthen cutters and provide consistent performance

Marketing Text 3

Effectively cuts most hardened wire, ACSR, bolts, screws and nails

Marketing Text 4

Through-hardened steel for longer life

Marketing Text 5

Dual cutting edges for optimum cutting performance

Marketing Text 6

Exceeds ASME/ANSI specifications

Marketing Text 7

Rugged riveted construction for smooth precise action

Marketing Text 8

Lifetime limited warranty

Marketing Text 9

Note: This is not an insulated tool

Marketing Text 10

Molded Grip Only: Custom grip allows area for user identification

Marketing Text 11

Flared handles for added comfort and leverage

Marketing Text 12

Wider grip design provides larger load bearing area for user comfort

PRODUCT SPECIFICATION –

Product Specification 1

Application : For Cutting Most Hardened Wire, ACSR, Bolts, Screws And Nails

Product Specification 2

Handle Type : Flared, Angled Molded Grip

Product Specification 3

Material : Chrome Vanadium Steel

Product Specification 4

Overall Length : 8-3/4 IN (22.200 CM)

Product Specification 5

Size : 8.000 IN

Product Specification 6

Standard : ASME/ANSI

Product Specification 7

Type : High Leverage Diagonal

Product Specification 8

Weight : 0.850 LB (0.390 KG)