

- ▶ Operates on programmed start electronic ballast except where otherwise identified
- ▶ TCLP compliant<sup>1</sup>



E-Lume  
F4T5/25K/8/PS/G5/ELUME  
SAR T5 Warm white 16mm dia

Dia. = 5/8 in. (16 mm)

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty
------------	-------------	-----------	------	------------------	-----	--------------------	---------------------	------------------	---------------------------	-----------------	----------

### T5 Preheat Start

56510	F6T5/CW/PH/G5/ELUME	6	Min Bipin	4 100	62	7 500	240	225	9 229	40	48
56511	F6T5/DL/PH/G5/ELUME	6	Min Bipin	6 500	62	7 500	210	197	9 229	35	48
56512	F8T5/CW/PH/G5/ELUME	8	Min Bipin	4 100	62	7 500	350	329	12 305	44	48
56513	F8T5/DL/PH/G5/ELUME	8	Min Bipin	6 500	62	7 500	310	291	12 305	39	48
56518	F13T5/WW/PH/G5/ELUME	13	Min Bipin	3 000	62	7 500	800	752	21 530	62	48
57392	F13T5/CW/PH/G5/ELUME	13	Min Bipin	4 100	62	7 500	740	695	21 530	57	48

\* Based on a 3 hour start \*\* Based on a 12 hour start

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life PS/PRS ballast 3-12 hrs	Initial lumens (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty
------------	-------------	-----------	------	------------------	-----	------------------------------------	---------------------	------------------	---------------------------	-----------------	----------


### T5 Program Start

59187 <sup>1</sup>	F14T5/35K/8/PS/G5/ELUME	14	Min Bipin	3 500	85	24 000* - 30 000**	1 350	1 280	22 559	96	25
59188 <sup>1</sup>	F14T5/41K/8/PS/G5/ELUME	14	Min Bipin	4 100	85	24 000* - 30 000**	1 350	1 280	22 559	96	25
59189 <sup>1</sup>	F14T5/50K/8/PS/G5/ELUME	14	Min Bipin	5 000	85	24 000* - 30 000**	1 300	1 230	22 559	93	25
59190 <sup>1</sup>	F21T5/35K/8/PS/G5/ELUME	21	Min Bipin	3 500	85	24 000* - 30 000**	2 100	2 000	34 864	100	25
59191 <sup>1</sup>	F21T5/41K/8/PS/G5/ELUME	21	Min Bipin	4 100	85	24 000* - 30 000**	2 100	2 000	34 864	100	25
59192 <sup>1</sup>	F21T5/50K/8/PS/G5/ELUME	21	Min Bipin	5 000	85	24 000* - 30 000**	2 100	2 000	34 864	100	25
59196 <sup>1</sup>	F28T5/35K/8/PS/G5/ELUME	28	Min Bipin	3 500	85	24 000* - 30 000**	2 900	2 750	46 1168	104	25
59197 <sup>1</sup>	F28T5/41K/8/PS/G5/ELUME	28	Min Bipin	4 100	85	24 000* - 30 000**	2 900	2 750	46 1168	104	25
59198 <sup>1</sup>	F28T5/50K/8/PS/G5/ELUME	28	Min Bipin	5 000	85	24 000* - 30 000**	2 750	2 610	46 1168	98	25

### T5 HO Program Start

59193 <sup>1</sup>	F24T5/35K/8/HO/PS/G5/ELUME	24	Min Bipin	3 500	85	24 000* - 30 000**	2 000	1 900	22 559	83	25
59194 <sup>1</sup>	F24T5/41K/8/HO/PS/G5/ELUME	24	Min Bipin	4 100	85	24 000* - 30 000**	2 000	1 900	22 559	83	25
59195 <sup>1</sup>	F24T5/50K/8/HO/PS/G5/ELUME	24	Min Bipin	5 000	85	24 000* - 30 000**	1 900	1 805	22 559	79	25
59199 <sup>1</sup>	F39T5/35K/8/HO/PS/G5/ELUME	39	Min Bipin	3 500	85	24 000* - 30 000**	3 500	3 325	34 864	90	25
59200 <sup>1</sup>	F39T5/41K/8/HO/PS/G5/ELUME	39	Min Bipin	4 100	85	24 000* - 30 000**	3 500	3 325	34 864	90	25
59201 <sup>1</sup>	F39T5/50K/8/HO/PS/G5/ELUME	39	Min Bipin	5 000	85	24 000* - 30 000**	3 500	3 325	34 864	90	25
63570 <sup>1</sup>	F54T5/41K/8/HO/PS/G5/ELUME	54	Min Bipin	4 100	85	24 000* - 30 000**	5 000	4 450	46 1168	92	25

# Fluorescent Lamps



- ▶ Higher initial and maintained lumens than conventional T12 lamps
- ▶ Better colour rendering
- ▶ TCLP compliant
- ▶ Available in a variety of colour temperatures



Dia. = 1 1/2 in. (26 mm)

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Mean lumens (lm)	Nominal length (in. / mm)		Efficacy (lm/W)	Case qty
------------	-------------	-----------	------	------------------	-----	--------------------	---------------------	------------------	---------------------------	--	-----------------	----------

### T8 Preheat Start

56514	F15T8/CW/PH/G13/ELUME	15	Med Bipin	4100	62	7500	610	573	18	457	41	48
56515	F15T8/DL/PH/G13/ELUME	15	Med Bipin	6500	72	7500	560	526	18	457	37	48

\* Based on a 3 hour start \*\* Based on a 12 hour start

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life on IS ballast 3-12 hrs	Rated life PS/PRS ballast 3-12 hrs	Initial lumens (lm)	Mean lumens (lm)	Nominal length (in. / mm)		Efficacy (lm/W)	Case qty
------------	-------------	-----------	------	------------------	-----	-----------------------------------	------------------------------------	---------------------	------------------	---------------------------	--	-----------------	----------

### T8 800 Series - Rapid Start

62513	F32T8/35K/8/RS/G13/ELUME/BULK	32	Med Bipin	3500	85	24 000* - 30 000**	40 000* - 42 000**	3 050	2 900	48	1 220	95	25
62514	F32T8/41K/8/RS/G13/ELUME/BULK	32	Med Bipin	4100	85	24 000* - 30 000**	40 000* - 42 000**	3 000	2 850	48	1 220	94	25
62515	F32T8/50K/8/RS/G13/ELUME/BULK	32	Med Bipin	5000	85	24 000* - 30 000**	40 000* - 42 000**	2 950	2 800	48	1 220	92	25
62516	F32T8/65K/8/RS/G13/ELUME/BULK	32	Med Bipin	6500	85	24 000* - 30 000**	40 000* - 42 000**	2 900	2 750	48	1 220	91	25



Dia. = 1 1/2 in. (29.5 mm)

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Mean lumens (lm)	Nominal length (in. / mm)		Efficacy (lm/W)	Case qty
------------	-------------	-----------	------	------------------	-----	--------------------	---------------------	------------------	---------------------------	--	-----------------	----------

### CIRCLINE Rapid Start

56516	FC8T9/CW/RS/4P/ELUME	22	Circline 4-Pin	4100	60	12 000	1 150	1 095	9	229	52	24
56517	FC12T9/CW/RS/4P/ELUME	32	Circline 4-Pin	4100	85	12 000	1 570	1 495	12	305	49	24