

# SVI – VIVIO™

## INFRARED PATIO HEATER

# ViVio™



## COMFORTABLY RADIANT!

Introducing Vivio, the ideal patio heater designed to extend your patio season from spring to fall. Vivio's infrared technology directs its heat rays precisely where you need them, quickly warming people and objects with unrivalled efficiency. Designed for terraces, outdoor waiting areas, spas and large, hard-to-heat indoor spaces, Vivio is versatile and practical. Thanks to its aluminum construction and stainless steel grid, it's sturdy and lightweight, which ensures outstanding durability and easy installation. Vivio – the ultimate solution for a warm, welcoming exterior all year round!

### REFINED DESIGN

DISCREET PROFILE AND PROTECTIVE GRILLE ALLOWS HEAT TO PASS THROUGH

### GENTLE SENSATION OF IMMEDIATE WARMTH

TEMPERATURE RISE IN LESS THAN 5 SECONDS

### OPTIMUM COMFORT FOR ALL ENVIRONMENTS

5 POWER LEVELS SELECTABLE BY REMOTE CONTROL

### HEAVY-DUTY CONSTRUCTION FOR OUTDOOR USE

EXTRUDED AND CAST ALUMINUM PARTS, STAINLESS STEEL GRILLE AND HARDWARE, IP65 WATER-RESISTANCE RATING

### EASY INSTALLATION

WITH DRILLING TEMPLATE AND ATTACHMENT SYSTEM DESIGNED FOR INSTALLATION BY ONE PERSON

### COLOUR

- Black

### FINISH

- Epoxy-polyester powdercoat

### MANUFACTURING

- 10-gauge equivalent aluminum extrusion housing
- Cast aluminum end cap
- Stainless steel grille
- 16-gauge stainless steel installation bracket
- Reflector to optimize radiation towards the user (symmetrical angle of 90°)
- Stainless steel installation hardware with black surface treatment

### LAMP

- Carbon filament infrared lamp
- Medium wavelength
- No glare
- Lifetime of over 5,000 hours

### CONTROL

- Remote control (stand included)
- 5 power levels
- Timer function

### INSTALLATION

- Surface-mounted on wall or ceiling with mounting bracket (included)
- 6' (1.83 m) minimum height
- Tilting and reversible unit (connection compartment on right or left)
- Discreet connection compartment
- Waterproof connector supplied (for flexible cable Ø 6.7 mm-12 mm/0.264 in-0.472 in)

### WARRANTY

- Three years

#### IDEAL FOR:

terraces, warehouses, factories, outdoor waiting areas, spas



# °STELPRO

Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website [www.stelpro.com](http://www.stelpro.com).

# TECHNICAL SPECIFICATIONS

PRODUCT	POWER	VOLTAGE	FREQUENCY	LENGTH		HEIGHT		DEPTH		SUPPORT DISTANCE		WEIGHT	
CODE	WATTS	VOLTS	HZ	MM	FT	MM	FT	MM	FT	MM	FT	KG	LB
<b>SVI1501BK</b>	1500	120	60	881	34-11/16	197	7-3/4	102	4	411	16-3/16	4.9	10.7
<b>SVI3002BK</b>	3000/2250	240/208	60	1122	44-3/16	197	7-3/4	102	4	652	25-5/8	5.9	13
<b>SVI4002BK</b>	4000/3000	240/208	60	1595	62-13/16	197	7-3/4	102	4	1071	42-3/16	8.3	18.3
<b>SVI6002BK</b>	6000/4500	240/208	60	2075	81-11/16	197	7-3/4	102	4	1551	61-1/16	10.4	22.9

## TYPE OF INSTALLATION AND HEATED AREA



PRODUCT	POWER	RECOMMENDED INSTALLATION HEIGHT* [A]		ELEVATION ZONE OF 10 °C [B x C]	
		M	FT	M	FT
<b>SVI1501BK</b>	1500	1.8 to 2.1	6 to 7	2.1 x 2.1	8 x 8
<b>SVI3002BK</b>	3000/2250	2.1 to 2.7	7 to 9	2.7 x 2.7	9 x 9
<b>SVI4002BK</b>	4000/3000	2.7 to 3	9 to 10	3.3 x 3.3	11 x 11
<b>SVI6002BK</b>	6000/4500	3 to 3.7	10 to 12	4 x 4	13 x 13

PRODUCT	POWER	RECOMMENDED INSTALLATION HEIGHT* [A]		ELEVATION ZONE OF 5 °C [B x C]	
		M	FT	M	FT
<b>SVI1501BK</b>	1500	1.8	8	2.4 x 1.8	7 x 6
<b>SVI3002BK</b>	3000/2250	2.1 to 2.4	8	2.7 x 2.1	9 x 7
<b>SVI4002BK</b>	4000/3000	2.4 to 2.7	8 to 9	3.3 x 2.4	11 x 8
<b>SVI6002BK</b>	6000/4500	2.7 to 3.3	9 to 11	4.2 x 3	13 x 9

\*Recommended in an open environment.

PRODUCT	*DISTANCE (END-TO-END**) - CEILING OR WALL		*DISTANCE (SIDE-TO-SIDE***) - CEILING ONLY	
	M	FT	M	FT
<b>SVI1501BK</b>	1.2	4	1.5	5
<b>SVI3002BK</b>	1.5	5	2.1	7
<b>SVI4002BK</b>	1.8	6	2.7	9
<b>SVI6002BK</b>	2.4	8	3.6	12


\*Distance to be respected to optimize the area covered by several devices while maintaining uniform comfort.

\*\*Elevation zone (end-to-end installation, ceiling or wall) = B x number of units x C


\*\*\*Elevation zone (side-by-side installation, ceiling only) = B x C x number of units

# TECHNICAL DRAWINGS


## 1500 W MODEL



BACK




SIDE




FRONT

SIDE


## 3000 W MODEL



BACK




SIDE




FRONT

SIDE


## 4000 W MODEL



BACK




SIDE




FRONT

SIDE


## 6000 W MODEL



BACK



SIDE



FRONT

SIDE





Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website [www.stelpro.com](http://www.stelpro.com).