

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

WPS GEN 5

CLASSIC WALL PACK

3 CCT and Power Selectable

Integrated Photocell

Multi-Voltage (120-347 V)

ORDERING INFORMATION

Order code: 70124
Model number: WPS-PS40B-Q-3C-WH
UPC: 069549031968
Case quantity: 1
DLC unique ID: S-C85MXX

PHYSICAL DATA

Lens material: Prismatic tempered glass lens
Finish: White
Housing material: Die cast aluminum
Photocell: Yes

PERFORMANCE DATA

Watts (W): 25/30/40
Volts (V AC): 120-347
Color temperature (K): 3 000/4 000/5 000
Lumen output (lm): 4010-5981
Efficacy (lm/W): 148-160
CRI: 80+
Life L70 (h): 50,000
Tested LM-80 (h): 9,000
Photocell included: Yes
Dimming: Yes
THD (%): 20
B.U.G.: 133
LED current (mA): 550
Power factor: 0.9
Operating temp. range: -40 °C to 50 °C (-40 °F to 122 °F)

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM80 testing report and projected per IESNA TM-21 extrapolations.

ACCESSORIES (order separately)

Order code	Description
69915	Wireguard
70126	White glaesshield



This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

CONFIGURABLE TECHNICAL SPECIFICATION TABLE

Order code	Model number	Watts (W)	3 000 K		4 000 K		5 000 K	
			Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
70124	WPS-PS40B-Q-3C-WH	25	3 855	150	4 010	160	4 083	157
		30	4 433	148	4 646	158	4 713	154
		40	5 691	139	5 981	148	5 831	143

DEFAULT PROGRAMMING

70124: 40 W / 4 000 K


DIMENSIONS AND WEIGHT

A in. (mm)	14.2" (360)
B in. (mm)	8.6" (218)
C in. (mm)	6.5" (164.5)
Net weight (lbs)	7.49

PHOTOMETRIC DATA¹

70124 • WPS-PS40B-W-3C-XX • 40 W • 4 000 K • 5 981 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 330.2	21.2
0-40	2 088.5	33.2
0-60	3 733.5	59.4
60-90	1 806.1	28.7
70-100	1 364.3	21.7
90-120	615.9	9.8
0-90	5 539.7	88.1
90-180	748.4	11.9
0-180	6 288.1	100

Illuminance at a distance

Center beam fc		Beam width	
8.3'	29.7 fc	21.0'	19.6'
16.7'	7.33 fc	42.3'	39.4'
25.0'	3.27 fc	63.3'	58.9'
33.3'	1.84 fc	84.3'	78.5'
41.7'	1.18 fc	105.5'	98.3'
50.0'	0.62 fc	126.5'	117.9'

■ Vert. spread: 103.4°
■ Horiz. spread: 99.4°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.