

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

WPS GEN 5

CLASSIC WALL PACK

3 CCT and Power Selectable

Integrated Photocell

Multi-Voltage (120-347 V)

ORDERING INFORMATION

Order code: 70125
Model number: WPS-PS100B-Q-3C-WH
UPC: 069549031975
Case quantity: 1
DLC unique ID: S-1PY77J

PHYSICAL DATA

Lens material: Prismatic tempered glass lens
Finish: White
Housing material: Die cast aluminum
Photocell: Yes

PERFORMANCE DATA

Watts (W): 60/80/100
Volts (V AC): 120-347
Color temperature (K): 3 000/4 000/5 000
Lumen output (lm): 8819-14554
Efficacy (lm/W): 153-156
CRI: 80+
Life L70 (h): 50,000
Tested LM-80 (h): 9,000
Photocell included: Yes
Dimming: Yes
THD (%): 20
B.U.G.: 345
LED current (mA): 410
Power factor: 0.9
Operating temp. range: -40 °C to 50 °C (-40 °F to 122 °F)

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM80 testing report and projected per IESNA TM-21 extrapolations.

ACCESSORIES (order separately)

Order code	Description
69915	Wireguard
70126	White glaesshield



ICES
005



CONFIGURABLE TECHNICAL SPECIFICATION TABLE

Order code	Model number	Watts (W)	3 000 K		4 000 K		5 000 K	
			Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
70125	WPS-PS100B-Q-3C-WH	60	8 678	149	8 819	154	8 699	149
		80	11 678	146	12 053	153	11 741	146
		100	13 574	142	14 554	156	13 676	143

DEFAULT PROGRAMMING

70125: 100 W / 4 000 K


DIMENSIONS AND WEIGHT

A in. (mm)	14.2" (360)
B in. (mm)	8.6" (218)
C in. (mm)	6.5" (164.5)
Net weight (lbs)	7.49

PHOTOMETRIC DATA¹

70125 • WPS-PS100B-W-3C-XX • 100 W • 4 000 K • 14 554 lm

Polar candela distribution



¹ Complete IES files available on our website.

Zonal lumen summary

Zone	Lumens	% Fixture
0-30	3 143.2	21.7
0-40	4 902.9	33.81
0-60	8, 682.7	59.81
60-90	4 080.0	28.1
70-100	3 064.9	21.1
90-120	1 436.1	9.9
0-90	12 762.8	87.9
90-180	1 749.2	12.1
0-180	14 512.0	100

Illuminance at a distance

Center beam fc		Beam width	
8.3'	70.0 fc	21.7'	18.7'
16.7'	17.3 fc	43.6'	37.7'
25.0'	7.71 fc	65.3'	56.4'
33.3'	4.35 fc	87.0'	75.1'
41.7'	2.77 fc	108.9'	94.1'
50.0'	1.93 fc	130.6'	112.8'

■ Vert. spread: 105.1°
■ Horiz. spread: 96.9°

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.