

# 3M™ Heat Shrink Tubing FP-301

## Flexible, Polyolefin

Data Sheet

November 2018

---

<b>Description</b>	<p>3M™ Heat Shrink Tubing FP-301 offers an excellent balance of electrical, physical and chemical properties for a wide variety of industrial and military applications. Rated for 135°C continuous operation, all 3M FP-301 tubing is split resistant, mechanically tough, easily marked and resists cold flow.</p> <p>3M FP-301 tubing is rated for continuous operation at -55°C (-67°F) to 135°C (275°F), and is designed to withstand elevated temperatures to 300°C (572°F) for short periods. Minimum shrink temperature for all 3M FP-301 tubing is 100°C (212°F).</p>
<b>Agency Approvals &amp; Self Certifications</b>	<p>Meets requirements of:</p> <ul style="list-style-type: none"><li>• AS23053/5, Class 1, Class 2 (Clear)*</li><li>• UL Recognized, File E-39100, at 600 volts maximum @ 125°C</li><li>• CSA Certified, CSA LR38227, at 600 volts maximum @ 125°C</li><li>• For RoHS and REACH information, please visit <a href="http://www.3M.com/regis">www.3M.com/regis</a></li></ul> <p>*Formerly MIL-I-23053/5, MIL-DTL-23053/5 and SAE-AMS-DTL-23053/5</p>
<b>Applications</b>	<p>3M FP-301 tubing is typically used as a shrink-fit electrical insulation over cable splices and terminations. It is also used for lightweight wire harness covering, wire marking, wire bundling, component packaging and fire-resistant covering.</p>
<b>Shrink Ratio</b>	<p>3M FP-301 tubing has a 2:1 shrink ratio. When freely recovered, the tubing will shrink to 50% of its as-supplied internal diameter. The recovered wall thickness is proportional to the degree of recovery.</p>

---

# 3M™ Heat Shrink Tubing FP-301

---

## Standard Sizes and Dimensions

Ordering Size (Nominal)	Expanded I.D. (Minimum)		Recovered I.D. (Maximum)		Recovered Wall Thickness (Nominal)	
	In.	(mm)	In.	(mm)	In.	(mm)
3/64	.046	(1,17)	.023	(0,58)	.016	(0,41)
1/16	.063	(1,60)	.031	(0,79)	.017	(0,43)
3/32	.093	(2,36)	.046	(1,17)	.020	(0,51)
1/8	.125	(3,18)	.062	(1,57)	.020	(0,51)
3/16	.187	(4,75)	.093	(2,36)	.020	(0,51)
1/4	.250	(6,35)	.125	(3,18)	.025	(0,64)
3/8	.375	(9,53)	.187	(4,75)	.025	(0,64)
1/2	.500	(12,70)	.250	(6,35)	.025	(0,64)
3/4	.750	(19,05)	.375	(9,53)	.030	(0,76)
1	1.000	(25,40)	.500	(12,70)	.035	(0,89)
1-1/2	1,500	(38,10)	.750	(19,05)	.040	(1,02)
2	2.000	(50,80)	1.000	(25,40)	.045	(1,14)
3	3.000	(76,20)	1.500	(38,10)	.050	(1,27)
4	4.000	(101,60)	2.000	(50,80)	.055	(1,40)

# 3M™ Heat Shrink Tubing FP-301

## Typical Properties

Not for specifications. Values are typical, not to be considered minimum or maximum. Properties measured at room temperature 73°F (23°C) unless otherwise stated.

Physical Property	Typical Value US units (metric)
Tensile Strength	2400 psi
Ultimate Elongation	400%
Longitudinal Change	±5%
Secant Modulus (2%)	13,000 psi
Specific Gravity	1.3 (Opaque) .93 (Clear)
Operating Temperature	-67° to 275°F (-55° to +135°C)
Shrink Temperature (minimum)	212°F (100°C)
Heat Aging (336 hrs. @ 175° C)	Elongation 175%
Heat shock (4 hrs. @ 250° C)	No dripping, flowing, cracking, passes mandrel wrap test
Low Temperature Flexibility (4 hrs @ -55° C)	No cracking
Scant Modules (2%)	13,000 psi
Flammability Self-extinguish, Meets UL 224 All-Tubing Flame Test (Except Clear)	Pass

Electrical Property (Test Method)	Typical Value
Dielectric Strength	900 V/mil
Volume Resistivity	10 <sup>15</sup> ohm/cm

Chemical Property (Test Method)	Typical Value
Corrosion Resistance (Copper mirror)	Non-corrosive
Fungus Resistance	Non-nutrient
Water Absorption	0.2%
Solvent Resistance	Excellent

## Standard Colors

Black, Clear

Also available in Blue, Green, Red, White and Yellow. Price, MOQ and Lead Time will vary for these colors. Please contact Local Sales Representative or Customer Service Representative for more information.

NOTE: The clear tubing is not flame retardant or UL listed.