



circular conduc. terminal TA2.8 1x250...750 kcmil; 2x250 kcmil for 1 cable 250 - 750 kcmil or 2 cables 250 kcmil 3 units accessory for: 3VA53/54; 3VA63/64 up to 400 A

Model		
product brand name	SETRON	
product designation	circular conductor terminal	
accessories	Wire connector	
General technical data		
designation / of the terminal	TA2.8	
type of electrical connection / with control wire tap	No	
Connections according IEC		
stripped length	38,1 mm	
Connections according UL		
permissible temperature / of connectable conductor / according to UL 486A-486B	90 °C	
stripped length	1.5 in	
connectable conductor cross-section		
<ul style="list-style-type: none"> • for copper cable / stranded / minimum • for copper cable / stranded / maximum • for aluminum cable / stranded / minimum • for aluminum cable / stranded / maximum 	250 kcmil 750 kcmil 250 kcmil 750 kcmil	
tightening torque / when using copper cables		
<ul style="list-style-type: none"> • stranded 	250-750 kcmil: 410.0 lb-in 250 kcmil: 410.0 lb-in	
Certificates		
General Product Approval	EMV	Marine / Shipping



[Miscellaneous](#)



other	Environment
Confirmation	Environmental Con- firmations
Miscellaneous	Environmental Con- firmations
Miscellaneous	

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
 Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>
 Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9373-0JJ24>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9373-0JJ24>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9373-0JJ24

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/27/2024

