





Key-operated switch O.M.R, 22 mm, round, plastic, lock number 73038, blue, with 2 keys, 2 switch positions O<I, momentary contact type, Actuating angle 45°, 10:30h/12h, Key removal O

product brand name	SIRIUS ACT
product designation	Key-operated switches
design of the product	Actuating/signaling element
product type designation	3SU1
product line	Plastic, black, 22 mm
manufacturer's article number of included key	3SU1950-0FJ50-0AA0
Actuator	
principle of operation of the actuating element	momentary contact, 45° (10:30 h/12 h), return from center to left
product extension optional light source	No
color	
• of the actuating element	blue
material of the actuating element	metal
shape of the actuating element	Key
outer diameter of the actuating element	29.5 mm
number of switching positions	2
switch position for key distraction	O
actuating angle	
• clockwise	45°
lock make	O.M.R.
key number	73038
Front ring	
product component front ring	Yes
design of the front ring	Standard
material of the front ring	plastic
color of the front ring	black
General technical data	
protection class IP	IP66, IP67, IP69(IP69K)
• of the terminal	IP20
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12, 13
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
• for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
• for railway applications according to EN 61373	Category 1, Class B
operating frequency maximum	1 800 1/h
mechanical service life (operating cycles) typical	1 000 000

reference code according to IEC 81346-2	S				
Substance Prohibittance (Date)	10/01/2014				
Ambient conditions					
ambient temperature					
• during operation	-25 ... +70 °C				
• during storage	-40 ... +80 °C				
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%)				
Environmental footprint					
Environmental Product Declaration(EPD)	Yes				
Global Warming Potential [CO2 eq] total	0.787 kg				
Global Warming Potential [CO2 eq] during manufacturing	0.566 kg				
Global Warming Potential [CO2 eq] during operation	0.235 kg				
Global Warming Potential [CO2 eq] after end of life	-0.015 kg				
Siemens Eco Profile (SEP)	Siemens EcoTech				
Installation/ mounting/ dimensions					
height	29.5 mm				
width	29.5 mm				
shape of the installation opening	round				
mounting diameter	22.3 mm				
positive tolerance of installation diameter	0.4 mm				
mounting height	51.7 mm				
installation width	29.5 mm				
installation depth	25.4 mm				
Approvals Certificates					
General Product Approval	other	Environment			
				Confirmation	Confirmation
Further information					
Information on the packaging					
https://support.industry.siemens.com/cs/ww/en/view/109813875					
Information- and Downloadcenter (Catalogs, Brochures,...)					
https://www.siemens.com/ic10					
Industry Mall (Online ordering system)					
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1000-4GC01-0AA0					
Cax online generator					
http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1000-4GC01-0AA0					
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)					
https://support.industry.siemens.com/cs/ww/en/ps/3SU1000-4GC01-0AA0					
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)					
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1000-4GC01-0AA0&lang=en					



last modified:

2/7/2024 