




PRODUCT-DETAILS

# XT3N 225 TMF 150-1500 3p F F UL/CSA

## XT3N 225 TMF 150-1500 3p F F UL/CSA



### General Information

Extended Product Type	XT3N 225 TMF 150-1500 3p F F UL/CSA
Product ID	1SDA075115R1
EAN	8015644790929
Catalog Description	XT3N 225 TMF 150-1500 3p F F UL/CSA
Long Description	C.BREAKER TMAX XT3N 225 UL/CSA FIXED THREE-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMF R 150-1500 A

### ABB EcoSolutions

ABB EcoSolutions	Yes
------------------	-----

### Circular Value

Circular Design Principles Recyclability Rate	Design for Closing Resource Loops - Standard EN45555 - 56.6 %
End of Life Instructions	9AKK108468A2350

Group Waste to Landfill Target

UL 2799 Zero Waste To Landfill Validation available

### Eco Transparency

Environmental Product Declaration - EPD 9AKK108468A2294

### Environmental

Environmental Information 9AKK108467A6707

### Material Compliance

REACH Declaration 9AKK108466A1425  
 RoHS Information 9AKK108466A1424  
 RoHS Status Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019  
 Conflict Minerals Reporting Template (CMRT) 9AKK108467A5658  
 Toxic Substances Control Act - TSCA 9AKK108467A8326

SCIP e564cbc2-abb5-4f89-b877-1d083ef422ee Italy (IT)  
 Simplified SCIP afbcfe8b-344d-4ab7-9884-553916000d8f Belgium (BE)  
 251a51ba-08c2-4782-86d2-f0321642fa1f Spain (ES)  
 a51cc241-2457-46ee-89a4-a63db4a278fe Hungary (HU)  
 67b6af89-015e-4f08-8106-50ebbb857414 Germany (DE)  
 79e11fc1-20ae-4213-bb8d-f4176cc81ff8 Croatia (HR)  
 b9210515-b7ca-4e22-a393-9a46b59a94ef Portugal (PT)  
 1da81ef7-7477-4666-88e4-c0dbe168dc81 Denmark (DK)  
 16b36251-028d-4a10-9df5-a9a86e83e118 Sweden (SE)  
 c1aafc9b-b5fb-4305-bc82-a43c7468a4a7 Germany (DE)  
 21e5bf67-2e05-4cc9-af03-c7f04082433e Germany (DE)  
 9c96382f-2599-43f4-88b1-49266fabf2de Czech Republic (CZ)  
 9b0dca4c-2e51-48eb-b5be-3aebc1e1f4b1 France (FR)  
 bea3670c-54fc-446d-8f61-923858430255 Greece (GR)  
 51b5f2fe-71de-4175-a321-1b9079edafcf Belgium (BE)  
 7c05eeee-7ed1-4626-8331-de529e0ff268 Poland (PL)  
 Oeacf34d-755c-4071-9bb4-3d6ee17ffcff Estonia (EE)  
 508184f3-db26-4518-b62e-cd55453b1e81 Germany (DE)  
 4ff1e5e7-b8dc-49e5-ac39-4f9fa56512a1 France (FR)  
 d87aa2c5-ab2a-4cfb-b674-256cf4e856f5 Bulgaria (BG)  
 bb6abc62-9135-45fd-a2bb-b45ec08b0ddd Hungary (HU)  
 95095274-9e95-491a-ab7c-bce5133c6836 Finland (FI)  
 4d60ba3f-f6ec-40d7-bc54-ab0fa7a2c696 Sweden (SE)  
 d05b77ba-b8b2-4d66-aa0b-181793625375 Norway (NO)  
 f8d69692-352d-4bc8-891e-9db152fd5570 Netherlands (NL)  
 989fbc9e-2257-427e-8669-f9a94848d387 Germany (DE)  
 c020c789-0caa-4fad-81a6-a2ae395148ff Poland (PL)  
 7a254d6f-6d22-466f-b5da-f4ee6a382fbf Poland (PL)

### Ordering

Order Code US and Canada XT3NU3150AFF000XXX  
 EAN 8015644790929  
 Minimum Order Quantity 1 piece  
 Customs Tariff Number 85362090

## Dimensions

Product Net Width	105 mm
Product Net Height	150 mm
Product Net Depth / Length	70 mm
Product Net Weight	1.7 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	155 mm
Package Level 1 Height	190 mm
Package Level 1 Depth / Length	155 mm
Package Level 1 Gross Weight	1.7 kg
Package Level 1 EAN	8015644790929

## Additional Information

Circuit Breaker Type to be Associated	Power Distribution
Product Main Type	SACE Tmax XT
Product Name	Moulded Case Circuit Breaker
Product Type	Automatic Circuit Breaker
Suitable for Product Class	SACE Tmax XT
Version	F
CAD Dimensional Drawing	1SDH001295R0409

## Technical

Connecting Capacity Main Circuit	Busbar 85..192 mm <sup>2</sup>
Current Type	AC/DC
Electrical Durability	120 cycles per hour 8000 cycle
Mechanical Durability	240 cycles per hour 25000 cycle
Number of Poles	3
Opening Time	CB with SOR 15 ms CB with UVR 15 ms
Order Multiple	1 piece
Power Loss	at Rated Operating Conditions per Pole 6.9 W
Rated Current (I <sub>n</sub> )	150 A
Rated Instantaneous Short-Circuit Current Setting (I <sub>i</sub> )	1500 A
Rated Operational Voltage	600Y/347 V AC 500 V DC
Rated Uninterrupted Current (I <sub>u</sub> )	225 A
Rated Voltage (U <sub>r</sub> )	600Y/347 V

Recommended Screw Driver	Main Circuit M8
Release	TMF
Release Type	TM
Setting Range	150 A
Short-Circuit Performance Level	N
Standards	UL489
Sub-type	XT3
Terminal Connection Type	Front
Terminal Type	Bolt
Tightening Torque	8 N·m

### Technical UL/CSA

Interrupting Rating acc. to UL489	(240 V AC) 50 kA (480 V AC) 25 kA (600Y / 347 V AC) 10 kA (250 V DC) 2 Poles in Series 25 kA (500 V DC) 3 Poles in Series 25 kA
-----------------------------------	---

### Certificates and Declarations

ATEX Certificate	No certification needed
CSA Certificate (Intrinsic Safe)	9AKK10103A3907
Data Sheet, Technical Information	1SDC210200D0206 1SDC210199D0206
Declaration of Conformity - CE	9AKK106713A5530
UL Certificate	1SDL000163R0113
VDE Certificate	No certification needed
Dimension Diagram	1SDH000720R0100
Mechanical Drawings	1SDH000720R0100
Wiring Diagram	1SDM000068R0001
Instructions and Manuals	1SDH000720R0003

### Classifications

ETIM 8	EC000228 - Power circuit-breaker for trafo/generator/installation protection
ETIM 9	EC000228 - Power circuit-breaker for trafo/generator/installation protection
IDEA Granular Category Code (IGCC)	4927 >> Molded case circuit breakers
Object Classification Code	Q
UNSPSC	39121616
WEEE Category eClass	5. Small Equipment (No External Dimension More Than 50 cm) V11.1 : 27370409

---

## Categories

---

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax XT

