

Project: _____

Type: _____

Drawn by: _____ Catalogue #: _____

Date: _____

*Individual Spec Sheet***LPDL™ ECO CHOICE****LED LOW PROFILE DOWNLIGHT**

4" CCT Selectable

ORDERING INFORMATION

Order code: 70144
Model number: LPDL4R-9A-5CWH-ECO/CHOICE
UPC: 069549032118
Case quantity: 50

PHYSICAL DATA

Size in (cm): 4 3/4 x 1 1/4 (12 x 1.8)
Shape: Round
Finish: White
Lens Type: Frosted polycarbonate
Mounting: Recessed

PERFORMANCE DATA

Watts (W): 9
Volts (V AC): 120
Color temperature (K)¹: 2 700/3 000/3 500/4 000/5 000
Lumen output (lm)²: 750
Efficacy (lm/W): 83.3
CRI: 80+
Life L70 (h)³: 50 000
Beam angle (°): 110
Environment: Wet location
THD (%): <20
Power factor: >0.9
Cable rating: FT4
Frequency (Hz): 60
Operating temp. range: -30 °C to 45 °C (-22 F° to 113 °F)
Dimmable: Phase cut (ELV / Triac)

¹ Typical colour temperature range: +/- 5 %.² Lumen values are derived from Energy Star reported data. Initial lumens range: +/- 10 %.³ Life hours are derived from IESNA LM-80 testing report and projected per IESNA TM-21 extrapolations.**LUMEN SPECIFICATION TABLE**

Watts	2 700 K		3 000 K		3 500 K		4 000 K		5 000 K	
(W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
9	767	85	809	90	857	95	868	96	829	92

DEFAULT PROGRAMMING

2 700 K


3^{yrs}
warranty
quick ship
LED fixture
dimnable fixture
airtight
wet location

IC rated

ICES 005


This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.
 Data is based upon tests performed in a controlled environment.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

ACCESSORIES (order separately)

Order code	Model number	Type
66821 ¹	ACC/MPLATE/4.25IN/HANG.BARS/STD	Mounting plate with hanger bars
66058	ACC/MPLATE/4.25/ADJ/STD	Adjustable mounting plate
66051	ACC/MPLATE/4.25/SQR/STD	Square mounting plate
66143	ACC/4/VAPOR BARRIER/STD	Vapor barrier extender
68986	GOOF RING-4.25IN	Goof rings

¹ Includes brackets and screws.


COMPATIBLE DIMMERS¹

Brand	Model
LEGRAND	RH730PTUTC
COOPER	AAL06, DAL06P, SAL06P3
LEVITON	6674, DDMX1, DSL06-1LZ, DSM10-1LZ, IPL06
LUTRON	AYCL-253P, DVCL-153P, DVCL-253P, DVELV-300P, HCL453P, MACL-153P, PD-6WCL, SELV-300P

Dimming range: 10%-100%

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.


DIMENSIONS AND WEIGHTS



PHOTOMETRIC DATA¹

70144 • LPDL4R-9A-5CWH-ECO/CHOICE • 3 000 K • 809.4 lm

Polar candela distribution



¹ Complete IES files available on our website.

Zonal lumen summary

Zone	Lumens	% Fixture
0-30	210.7	26
0-40	350.2	43.3
0-60	631.3	78
60-90	177.7	22
70-100	77.0	9.5
90-120	0.4	0.1
0-90	809.0	99.9
90-180	0.4	0.1
0-180	809.4	100

Illuminance at a distance

Center beam fc	Beam width
1.7'	91.6
3.3'	24.3
5.0'	10.6
6.7'	5.90
8.3'	3.84
10.0'	2.65
Vert. spread: 117.2°	Beam width
Horiz. spread: 115.9°	5.6'
	5.4'
	10.8'
	10.5'
	16.4'
	16.0'
	22.0'
	21.4'
	27.2'
	26.5'
	32.8'
	31.9'

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.