


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT2H	.188 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	8.1 (206)	120 (534)	HEAVY	STRAIGHT	.76 (346)
PLT2.5H	.188 (4.8)	2.50 (64)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	9.8 (251)	120 (534)	HEAVY	STRAIGHT	.90 (408)
PLT3H	.188 (4.8)	3.00 (76)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	11.4 (290)	120 (534)	HEAVY	STRAIGHT	1.04 (472)
PLT4H	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	14.5 (368)	120 (534)	HEAVY	STRAIGHT	1.28 (581)
PLT5H	.188 (4.8)	5.00 (127)	.078 (2.0)	.350 (8.9)	.406 (10.1)	.340 (8.6)	.560 (14.2)	17.7 (450)	175 (778)	HEAVY	STRAIGHT	2.06 (934)
PLT6H	.188 (4.8)	6.00 (152)	.078 (2.0)	.350 (8.9)	.406 (10.1)	.340 (8.6)	.560 (14.2)	20.9 (530)	175 (778)	HEAVY	STRAIGHT	2.46 (1116)
PLT8H	.188 (4.8)	9.00 (229)	.078 (2.0)	.350 (8.9)	.406 (10.3)	.340 (8.6)	.560 (14.2)	30.6 (779)	175 (778)	HEAVY	STRAIGHT	3.36 (1524)
PLT13H	5.50 (140)	13.00 (330)	.078 (2.0)	.350 (8.9)	.406 (10.3)	.340 (8.6)	.560 (14.2)	43.3 (1100)	175 (778)	HEAVY	STRAIGHT	4.59 (2080)

NOTE:

*SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	DRAWN BY	DATE	CHK	SCALE	SIZE	
							PREMIUM CABLE TIES - PLT SERIES	CEW	12-27-84	HVP	NONE	A	
							CUSTOMER DRAWING						
							ITEM REVISION NAME						
							W10001CD/11						
							DATASET FILE NAME						
							W10001CD_DC/11-SS-5540 SH4 r11A						
11A	10.02.24	BWG	JADE	DJSL	UPDATED TITLE BLOCK WITH ALTERNATE DESCRIPTION	005806/00	PANDUIT MATERIAL: NYLON 6.6 DRAWING NUMBER: SS-5540 SHEET 4						
10	4/04/14	BWG	MPH	JADE	UPDATED NOTES.	SS-5540/10		UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)					
09	8/13/13	BWG	KJM	RTFI	UPDATED TITLE BORDER.	SS-5540/09		.x ± --- .xxx ± .020 (.51) .xx ± .02 (.5) ANGLES ± ---					
							THIRD ANGLE PROJECTION						

D10100DA/16