

Data Sheet | Item Number: 750-497

8-channel analog input; 0 ... 10 V/±10 VDC; Single-ended

<https://www.wago.com/750-497>



This analog input module processes standard 0–10 VDC and ±10 V signals. The input signal is electrically isolated and is transmitted with a resolution of 12 bits. An out-of-measurement range is indicated by a red LED. Unused channels can be deactivated. The module can be configured via WAGO-I/O-CHECK or GSD files. It features an extremely compact design and low measurement errors.

Technical data

Number of analog inputs	8
Total number of channels (module)	8
Signal type	Voltage
Signal type (voltage)	0 ... 10 VDC; -10 ... +10 VDC
Signal type (configurable)	Yes
Sensor connection	8 x (2-wire)
Input voltage (max.)	35 V
Resolution [bit]	12 bits
Data width	8 x 16-bit data; 8 x 8-bit control/status (optional)
Internal resistance	100 kΩ
Measurement error (reference temperature)	25 °C
Measurement error, deviation (max.) from the upper-range value	0.1 %
Temperature error (max.) of the upper-range value	0.01 %/K
Configuration options	WAGO-I/O-CHECK CODESYS Library e!COCKPIT
Supply voltage (system)	5 VDC; via data contacts
Current consumption (5 V system supply)	105 mA
Supply voltage (field)	24 VDC (-25 ... +30 %); via power jumper contacts (power supply via blade contact; transmission (supply voltage field side only) via spring contact)
Isolation	500 V system/field
Indicators	LED (1-8) green: Status AI 1 ... AI 8; LED (9-16) red: Error AI 1 ... AI 8
Number of incoming power jumper contacts	2
Number of outgoing power jumper contacts	2

Connection data

Connection technology: inputs/outputs	16 x Push-in CAGE CLAMP®
Connection type 1	Inputs/outputs
Solid conductor	0.08 ... 1.5 mm ² / 28 ... 16 AWG
Fine-stranded conductor	0.25 ... 1.5 mm ² / 22 ... 16 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Physical data

Width	12 mm / 0.472 inches
Height	100 mm / 3.937 inches
Depth	69 mm / 2.717 inches
Depth from upper-edge of DIN-rail	61.8 mm / 2.433 inches

Mechanical data

Mounting type	DIN-35 rail
---------------	-------------

Material data

Housing material	Polycarbonate; polyamide 6.6
Fire load	0.837 MJ
Weight	51.5 g
Conformity marking	CE

Environmental requirements

Ambient temperature (operation)	0 ... +55 °C
Ambient temperature (storage)	-40 ... +85 °C
Protection type	IP20
Pollution degree	2 per IEC 61131-2
Operating altitude	0 ... 2000 m / 0 ... 6562 ft
Mounting position	Horizontal left, horizontal right, horizontal up, horizontal down, vertical top and vertical bottom
Relative humidity (without condensation)	95 %
Vibration resistance	4g per IEC 60068-2-6
Shock resistance	15g per IEC 60068-2-27
EMC immunity to interference	per EN 61000-6-2
EMC emission of interference	per EN 61000-6-3
Exposure to pollutants	per IEC 60068-2-42 and IEC 60068-2-43
Permissible H ₂ S contaminant concentration at a relative humidity 75 %	10 ppm
Permissible SO ₂ contaminant concentration at a relative humidity 75 %	25 ppm

Commercial data

eCl@ss 10.0	27-24-26-01
eCl@ss 9.0	27-24-26-01
ETIM 9.0	EC001596
ETIM 8.0	EC001596
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143350389
Customs tariff number	85389099990

Environmental Product Compliance	
CAS-No.	1303-86-2 1317-36-8 7439-92-1
REACH Candidate List Substance	Diboron trioxide Lead Lead monoxide
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c) 7(a) 7(c)-I 7(c)-II
SCIP notification number (Austria)	38de749d-60e7-4ae0-8a6c-b7904631cc54
SCIP notification number (Belgium)	617d2eee-1051-47a5-a6f3-241ffc99cd81
SCIP notification number (Bulgaria)	ec0fec79-db68-4962-8b63-e4c7fa14ed75
SCIP notification number (Czech Republic)	a8030d24-0aaa-40ba-8889-6fb64f1f7369
SCIP notification number (Denmark)	f7502ecb-a254-45cd-afe6-998813d77656
SCIP notification number (Finland)	b5c5226d-727b-44e3-b399-5758985b3d61
SCIP notification number (France)	3cfd4907-984d-4011-9458-2cc7b41c0686
SCIP notification number (Germany)	874938e3-f716-48cb-809e-60271ce1949b
SCIP notification number (Hungary)	dbe4bef0-4e14-490d-bc6c-9884adfea47b
SCIP notification number (Italy)	a340c2a5-4e3b-44c9-a071-bdfdecf7878c
SCIP notification number (Netherlands)	c7044e74-e017-41f8-b9be-7984d9467ca3
SCIP notification number (Poland)	68af4241-5680-43d6-b427-21db7e324d80
SCIP notification number (Romania)	90270177-f50c-416f-b6f4-64291fd3831d
SCIP notification number (Sweden)	de69e8e7-6046-4fdc-939a-c044525c1cb6