


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]				
	ENGLISH	METRIC	L ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
PMV6-3R	--	M3	1.02 [26,0]	.23 [5,8]	.31 [7,8]	.89 [22,61]	.13 [3,3]
PV10-6R	#6	M3,5	1.05 [26,7]	.31 [7,9]	.31 [7,9]	.89 [22,6]	.15 [3,8]
PV10-8R	#8	M4	1.05 [26,7]	.31 [7,9]	.31 [7,9]	.89 [22,6]	.17 [4,3]
PV10-10R	#10	--	1.05 [26,7]	.31 [7,9]	.31 [7,9]	.89 [22,6]	.20 [5,1]
PMV6-5R	--	M5	1.07 [27,1]	.37 [9,5]	.31 [7,8]	.89 [22,61]	.21 [5,3]
PV10-14R	1/4"	M6	1.23 [31,2]	.52 [13,2]	.38 [9,7]	.97 [24,6]	.27 [6,9]
PV10-56R	5/16"	M8	1.23 [31,2]	.52 [13,2]	.38 [9,7]	.97 [24,6]	.33 [8,4]
PV10-38R	3/8"	--	1.31 [33,3]	.58 [14,7]	.41 [10,4]	1.02 [25,9]	.39 [9,9]
PV10-12R	1/2"	--	1.46 [37,1]	.72 [18,3]	.53 [13,5]	1.10 [27,9]	.52 [13,2]

UL & CSA APPROVED TOOLS

CT-100B - #12-10 AWG
 CT-1550 - #14-10 AWG
 CT-1551 - #14-10 AWG
 CT-2300 - #14-10 AWG
 CT-2500 (CT-2550CH) - #14-10 AWG

METRIC EQUIVALENT
 #14 AWG = 2,5mm
 #12 AWG = 4,0 mm
 #10 AWG = 6,0 mm



NOTES:

- UL 486A/B LISTED & CSA C22.2 NO. 65-03 CERTIFIED FOR:
 - SOLID OR STRANDED COPPER WIRE
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600V. MAX. BLDG WIRE. (1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)
 - SOME TOOLS HAVE EXPANDED WIRE SIZES. SEE TOOL TABLES FOR AWG WIRE SIZES SUPPORTED BY EACH TOOL.
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES.
- MATERIAL:
 - STAMPING: .04" [1,0] THK COPPER, TIN PLATED
 - HOUSING: VINYL, YELLOW
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT.
- WIRE STRIP LENGTH: 5/16 ^{+1/32} [7,9 ^{+0,8}]



PART NUMBER		SEE TABLE	
TITLE			
RING TERMINALS, 2-PC VINYL INSULATED, #12-10			
CUSTOMER DRAWING			
ITEM REVISION NAME		N41187BA/10	
DATASET FILE NAME		N41187BA-DS r10A	
MATERIAL		SEE NOTES	
DRAWN BY		FES	
DATE		-	
CHK		LCA	
SCALE		N.T.S.	
DRAWING NUMBER		A41187	
SHEET 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
10A	07-31-24	DPOI	ACC	GSI	PMV6-3R & PMV6-5R UL LISTED NOW. NOTES UPDATED. ADDED TOOLS CHART & METRIC EQUIVALENT NOTE. UPDATED cULus LOGO.	078745/01
09	04-23-20	HPR	CLN	JADE	REV NUMBER CORRECTED FROM 7 TO 8	078745
08	06-07-12	BDK	LCA	VMB	REVISED PACKAGING NOTE. REVISED "USED FOR" NOTE. REMOVED PACKAGING CODE FROM CHART. ADDED PMV6-3R AND PMV6-5R TO CHART. ADDED INSTALLATION TOOL NOTE.	A41187

A-SIZE CUSTOMER