

Project: \_\_\_\_\_ Type: \_\_\_\_\_

Drawn by: \_\_\_\_\_ Catalogue #: \_\_\_\_\_ Date: \_\_\_\_\_

## Individual Spec Sheet

# LED REFLECTORS

## DESIGN PAR30SN

### ORDERING INFORMATION

**Order code:** 70215  
**Model number:** P30S/S2/10W/40K/40/DESIGN/STD  
**UPC:** 069549032682  
**Case quantity:** 20

### PHYSICAL DATA

**Dimensions:** MOL: 9 cm (3 1/2")  
 DIA: 9.5 cm (3 3/4")  
**Shape:** PAR30SN  
**Base:** E26  
**Finish:** Silver

### PERFORMANCE DATA


<b>Watts (W):</b>	10	<b>Beam angle (°):</b>	40°
<b>Traditional equivalent (W):</b>	60	<b>CBCP (cd):</b>	1 645
<b>Volts (V AC/DC):</b>	120	<b>Power factor:</b>	≥0.7
<b>Color temperature (K):<sup>1</sup></b>	4 000	<b>Input Current (mA):</b>	105
<b>Lumen output (lm)<sup>2</sup>:</b>	750	<b>Frequency (Hz):</b>	60
<b>Efficacy (lm/W):</b>	75	<b>Lens material:</b>	Glass
<b>CRI:</b>	80	<b>Housing Material:</b>	Glass
<b>Dimmable:</b>	Triac dimming	<b>Application:</b>	Indoor
<b>Life L70 (h)<sup>3</sup>:</b>	25 000	<b>Operating temp. range:</b>	- 40 °C / - 40 °F to 45 °C / 113 °F

<sup>1</sup> Typical colour temperature range: +/- 5 %.

<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

<sup>3</sup> Life hours are derived from IESNA LM-80 testing report and projected per IESNA TM-21 extrapolations.

### DIMENSIONS



### COMPATIBLE DIMMERS<sup>1</sup>

Brand	Model
LUTRON	HCL453P*, DVCL-153P*, CTCL-153P
COOPER	DAL06P
LEVITON	6615

\*Flickering may occur on low intensity

<sup>1</sup> This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

Dimming performance might be impacted when using the above dimmers with only one lamp. Full performance achieved when using two or more lamps.



**3**<sup>yrs</sup>  
warranty

**66**  
wet location

dimmable

not suitable for enclosed fixture

ICES 005

CERTIFIED