

Project: _____

Type: _____

Drawn by: _____ Catalogue #: _____

Date: _____

Individual Spec Sheet

L2SNQ

LED SLIM STRIP WITH SQUARE LENS

3 CCT and 3 Power Selectable

ORDERING INFORMATION

Order code: 69852
Model number: L2SNQ-96LP90-Q/3C-BK
UPC: 069549030725
Case quantity: 1
DLC unique ID: S-5GY3QJ¹ (DLC Premium) / S-NZDVMN² & S-QSW331³ (DLC Standard)

PHYSICAL DATA

Length in. (cm): 94 1/8 (239.2)
Lens material: Frosted PMMA
Housing material: 24 gauge matte black powder painted steel
Mounting: Surface, suspended or row mounted (Junction box cover included)

PERFORMANCE DATA

Watts (W): 65/75/90
Volts (V AC): 120-347
Color temperature (K)¹: 3 500/4 000/5 000
Lumen output (lm)²: 9 620/10 800/12 600
Efficacy (lm/W): 140
CRI: 80+
Life L70 (h)³: 156 000
Tested LM-80 (h)³: 9 000
Dimming: 0-10 V
Power factor: 0.90
THD (%): 10
Frequency (Hz): 50/60
Surge protection (kV): 2.5
Input current (A): 0.542-0.187/0.625-0.216/0.750-0.259
Operating temp. range: -20 °C to 50 °C (-4 °F to 122 °F)

¹ Typical colour temperature range: +/- 5 %.

² Lumen values are based on 4 000 K default programming.

Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.

³ Life hours are derived from IESNA LM-80 testing report and projected per IESNA TM-21 extrapolations.

LUMEN SPECIFICATION TABLE

Watts (W)	3 500 K		4 000 K		5 000 K	
	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)	Lumen output (lm)	Efficacy (lm/W)
65	8 970	138	9 620	148	8 970	138
75	10 050	134	10 800	144	10 050	134
90	11 700	130	12 600	140	11 700	130


DEFAULT PROGRAMMING

90 W / 4 000 K

This lighting equipment meets requirements of ICES-005 issue 5 class A for use in commercial applications.

Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.



Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.

¹ Stairwell And Passageway Luminaires

² Direct Linear Ambient Luminaires

³ High-Bay Luminaires for Commercial and Industrial Buildings

ACCESSORIES (order separately)

Order code	Type
69992	V-Hooks (Set of 2)
68676	Suspension kit - 2 chains (1 m) ¹
69082	10' Aviation cable kit with canopy, power cord & dimming wires - White
69906	Continuous row mounting connector - Black
69897	Wire guard kit 48" - White ²
69904	Replacement lens 96"

¹ Must be used in conjunction with 69992.
² For 96" luminaires, order 2 units.

INCLUDED IN THE BOX



Junction Box Cover


COMPATIBLE DIMMERS¹

Brand	Model
Leviton	IlumaTech IP710-LFZ
	Decora DS710-10Z
Lutron	Nova T NTSTV-DV
	Nova NFTV
	Diva DVSTV
Legrand	RH4FBL3PW

Dimming range: 10%-100%

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.


DIMENSIONS AND WEIGHT



PHOTOMETRIC DATA¹

69852 • L2SNQ-96LP90-Q/3C-BK • 65 W • 4 000 K • 10 310.7 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 951.2	18.9
0-40	3 234.1	31.4
0-60	5 945.5	57.7
60-90	2 579.2	25
70-100	1 869.0	18.1
90-120	1 149.4	11.1
0-90	8 524.7	82.7
90-180	1 786.1	17.3
0-180	10 310.7	100

Illuminance at a distance

	Center beam fc	Beam width	
2.0'	614.8	5.7'	12.1'
4.0'	153.7	11.5'	24.1'
6.0'	68.3	17.2'	36.2'
8.0'	38.4	23.0'	48.2'
10.0'	24.6	28.7'	60.3'

■ Vert. spread: 110.3°
■ Horiz. spread: 143.3°


¹ Complete IES files available on our website.

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

PHOTOMETRIC DATA¹

69852 • L2SNQ-96LP90-Q/3C-BK • 75 W • 4 000 K • 11 634.4 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	2 201.6	18.9
0-40	3 649.3	31.4
0-60	6 708.7	57.7
60-90	2 910.3	25
70-100	2 108.9	18.1
90-120	1 296.9	11.1
0-90	9 619.0	82.7
90-180	2 015.3	17.3
0-180	11 634.4	100


Illuminance at a distance

Center beam fc		Beam width	
2.0'	693.7	5.7'	12.1'
4.0'	173.4	11.5'	24.1'
6.0'	77.1	17.2'	36.2'
8.0'	43.4	23.0'	48.2'
10.0'	27.7	28.7'	60.3'

■ Vert. spread: 110.3°
■ Horiz. spread: 143.3°

69852 • L2SNQ-96LP90-Q/3C-BK • 90 W • 4 000 K • 13 645.8 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	2 582.3	18.9
0-40	4 280.2	31.4
0-60	7 868.6	57.7
60-90	3 413.4	25
70-100	2 473.5	18.1
90-120	1 521.1	11.1
0-90	11 282.0	82.7
90-180	2 363.8	17.3
0-180	13 645.8	100

Illuminance at a distance

Center beam fc		Beam width	
2.0'	813.6	5.7'	12.1'
4.0'	203.4	11.5'	24.1'
6.0'	90.4	17.2'	36.2'
8.0'	50.9	23.0'	58.2'
10.0'	32	28.7'	60.3'

■ Vert. spread: 110.3°
■ Horiz. spread: 143.3°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.