

Data Sheet | Item Number: 857-354

Relay module; Nominal input voltage: 24 V AC/DC; 1 changeover contact; Limiting continuous current: 6 A; Yellow status indicator; Module width: 6 mm

<https://www.wago.com/857-354>



Notes	
Safety Information	Adjacent devices of the same type are devices of the same design (series) that are arranged next to one another on the DIN-rail with the same orientation. An end stop (249-116) must be fitted to devices of other types for compliance with the reinforced insulation requirements.
Note	To protect the relay coils and contacts, inductive loads must be dampened with an effective protection circuit.

Technical data			
Control circuit		Load circuit	
Nominal input voltage U _N	24 VAC/VDC	Number of changeover/switchover contacts	1
Input voltage range	-15 ... +20 %	Contact material (relay)	AgSnO ₂
Nominal input current at U _N	9 mA	Limiting continuous current	6 A
Nominal frequency range (input voltage)	50 ... 60 HzAC / 0 HzDC	Inrush current (resistive) max.	(AC) 20 A / 0.02 s
		Switching Voltage, Max.	250 VAC
		Switching power (resistive) max.	AC 1500 VA; DC (see load limit curve)
		Switching capacity	AC-15: 3 A / 250 VAC; DC-13: 2 A / 24 VDC
		Recommended minimum load	10 V / 10 mA; 24 V / 1 mA
		Pull-in time (typ.)	15 ms
		Drop-out time (typ.)	25 ms
		Bounce time (typ.)	3.5 ms
		Electrical life (NO; resistive load; 23 °C)	50 x 10 ³ switching operations
		Mechanical life	5 x 10 ⁶ switching operations
		Switching frequency with/without load (max.)	6 min ⁻¹ / 180 min ⁻¹
		Short circuit protection (load circuit)	4 A; Fast (F)

Signaling	
Status indicator	Yellow LED

Safety and protection	
Rated Voltage	300 V
Rated impulse withstand voltage	4 kV
Type of circuits	Mains circuits
Overvoltage category	III
Pollution degree	2
Dielectric strength (control/load circuit) (AC, 1 min)	3.51 kVrms
Dielectric strength (open contact) (AC, 1 min)	1 kVrms
Insulation type (control/load circuit)	Reinforced insulation (safe isolation)
Insulation type (between adjacent devices of the same type)	Double insulation (safe isolation)
Insulation type (to adjacent devices of different types)	Basic insulation
Safety Information	Adjacent devices of the same type are devices of the same design (series) that are arranged next to one another on the DIN-rail with the same orientation. An end stop (249-116) must be fitted to devices of other types for compliance with the reinforced insulation requirements.
Protection type	IP20



Connection data	
Connection technology	Push-in CAGE CLAMP®
Solid conductor	0.34 ... 2.5 mm² / 22 ... 14 AWG
Fine-stranded conductor	0.34 ... 2.5 mm² / 22 ... 14 AWG
Fine-stranded conductor; with insulated ferrule	0.34 ... 1.5 mm² / 22 ... 16 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches

Physical data	
Width	6 mm / 0.236 inches
Height	94 mm / 3.701 inches
Depth from upper-edge of DIN-rail	81 mm / 3.189 inches

Mechanical data	
Mounting type	DIN-35 rail
Mounting position	horizontal (standing/lying); vertical

Material data	
Note (material data)	Information on material specifications can be found here
Insulation material (main housing)	Polyamide (PA66)
Material group	I
Flammability class per UL94	V0
Fire load	0.544 MJ
Weight	30.9 g

Environmental requirements	
Ambient temperature (operation at U _N)	-40 ... +60 °C
Ambient temperature (storage)	-40 ... +70 °C
Processing temperature	-25 ... +50 °C
Temperature range of connection cable	≥ (T _{ambient} + 30 K)
Relative humidity	5 ... 85 % (no condensation permissible)
Operating altitude (max.)	2000 m

Standards and specifications	
Standards/specifications	EN 61010-2-201 EN 61810-1 EN 61373 UL 508 ATEX IECE _x

Basic relay	
WAGO Basic Relay	857-152



Commercial data		
Product Group	6 (INTERFACE ELECTRONIC)	
eCl@ss 10.0	27-37-16-01	
eCl@ss 9.0	27-37-16-01	
ETIM 9.0	EC001437	
ETIM 8.0	EC001437	
PU (SPU)	25 (1) pcs	
Packaging type	Box	
Country of origin	CN	
GTIN	4055143122061	
Customs tariff number	85364900990	

Environmental Product Compliance		
CAS-No.	1303-86-2 7439-92-1 79-94-7	
REACH Candidate List Substance	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol Diboron trioxide Lead	
RoHS Compliance Status	Compliant,With Exemption	
RoHS Exemption	7(a)	
SCIP notification number (Austria)	1d57e8bb-d2c8-4bbb-8127-3643dd88a6f8	
SCIP notification number (Belgium)	2911a0a7-bd93-47c9-9b55-6366486afecf	
SCIP notification number (Bulgaria)	0aa902f5-f537-4125-a0b2-2e0c80eb9a54	
SCIP notification number (Czech Republic)	e99f0a97-d331-4447-b3f5-3ba7eb176298	
SCIP notification number (Denmark)	5089b3a6-0464-4cf8-a7e4-524370ed51e1	
SCIP notification number (Finland)	9d0eb0d1-335b-4fd7-89a3-fc2112beccad	
SCIP notification number (France)	8a209879-2cbe-4438-a8a4-d864505af01c	
SCIP notification number (Germany)	2505d55b-f52b-45fd-9b9c-34fd870b22eb	
SCIP notification number (Hungary)	443a377f-adfe-458c-acbf-10b9a603939a	
SCIP notification number (Italy)	050e301e-0f85-4e58-8c6a-218a0aef024	
SCIP notification number (Netherlands)	ffddf60-d420-4cd4-8610-03de8056ee6b	
SCIP notification number (Poland)	0a301502-1133-4d6e-a50a-b508449592d4	
SCIP notification number (Romania)	03812214-78b7-48c6-92d4-aa6bd90d9367	
SCIP notification number (Sweden)	3f803bb3-8f2d-487d-a36f-3df00d456667	