

# Plug Fuses



Mersen Plug Fuses are for industrial and residential applications. Standard non-time delay fuses are for receptacle and lighting circuits. For Canadian requirements, a type “P” fuse is used for non-motor loads and type “D” fuses are used for electric heating and cycling loads circuits. Both fuses have low melting-point temperature elements. Low-Temp time delay plug fuses have thermal sensitivity are also for cycling loads and motor circuits.

## TYPE S PLUG FUSE ADAPTORS

Type S adaptors screw into the Edison base and allow Type S fuses to be installed. Type S adaptors prevent the wrong ampere size fuse from being used.



Cat. No./Rating	Description
SAG1	1A TYPE S PLUG FUSE ADAPTER
SAG1-1/4	1-1/4A TYPE S PLUG FUSE ADAPTE
SAG1-6/10	1-6/10A TYPE S PLUG FUSE ADAPTER
SAG2	2A TYPE S PLUG FUSE ADAPTER
SAG2-1/2	2-1/2A TYPE S PLUG FUSE HOLDER
SAG5	5A TYPE S PLUG FUSE ADAPTER
SAG6-1/4	6-1/4A TYPE S PLUG FUSE ADAPTER
SAG10	10A TYPE S PLUG FUSE ADAPTER
SAG15	15A TYPE S PLUG FUSE ADAPTER
SAG30	30A TYPE S PLUG FUSE ADAPTER

## RATINGS:

- **Volts:** 125VAC
- **Amps:** 15A to 30A
- **IR:** 10kA I.R. AC
- Choice of Edison Base, Types “P” or “D”

## APPROVALS:

- CSA Certified Class 142301, File 15525



# Plug Fuses

## CATALOG NUMBERS (AMPS)

Cat. No./Rating	Description
GP15	125V 15A P PLUG FUSE
GP15-2C	FUSE PLUG
GP20	125V 20A P PLUG FUSE
GP20-2C	FUSE PLUG
GP25	125V 25A P PLUG FUSE
GP25-2C	FUSE PLUG
GP30	125V 30A P PLUG FUSE
GP30-2C	FUSE PLUG
S-1	125V 1A TYPE S PLUG FUSE
S-1/2	125V 1/2A TYPE S PLUG FUSE
S-1/4	125V 1/4A TYPE S PLUG FUSE
S-10	125V 10A TYPE S PLUG FUSE
S-1-1/4	125V 1-1/4A TYPE S PLUG FUSE
S-1-1/8	125V 1-1/8A TYPE S PLUG FUSE
S-14	125V 14A TYPE S PLUG FUSE
S-1-4/10	125V 1-4/10A TYPE S PLUG FUSE
S-1-6/10	125V 1-6/10A TYPE S PLUG FUSE
S-1-8/10	125V 1-8/10A TYPE S PLUG FUSE
S-2	125V 2A TYPE S PLUG FUSE
S-2-1/2	125V 2-1/2A TYPE S PLUG FUSE
S-2-1/4	125V 2-1/4A TYPE S PLUG FUSE
S-25	125V 25A TYPE S PLUG FUSE
S-2-8/10	125V 2-8/10A TYPE S PLUG FUSE
S-3	125V 3A TYPE S PLUG FUSE
S-30	125V 30A TYPE S PLUG FUSE
S-3-1/2	125V 3-1/2A TYPE S PLUG FUSE
S-3-2/10	125V AC, 3-2/10A TYPE S PLUG F
S-4	125V 4A TYPE S PLUG FUSE
S-4/10	125V 4/10A TYPE S PLUG FUSE
S-4-1/2	125V 4-1/2A TYPE S PLUG FUSE
S-5	125V 5A TYPE S PLUG FUSE
S-5-6/10	125V 5-6/10A TYPE S PLUG FUSE
S-6	125V 6A TYPE S PLUG FUSE
S-6/10	125V 6/10A TYPE S PLUG FUSE
S-6-1/4	125V AC, 6-1/4A TYPE S PLUG FU
S-7	125V 7A TYPE S PLUG FUSE
S-8	125V AC, 8A TYPE S PLUG FUSE
S-8/10	125V 8/10A TYPE S PLUG FUSE
S-9	125V 9A TYPE S PLUG FUSE

FR15 Rejector Rings available

FRW Rejection removal tool available to remove FR15

Cat. No./Rating	Description
T-1/2	125V 1/2A TYPE T PLUG FUSE
T-1-1/4	125V 1-1/4A TYPE T PLUG FUSE
T-1-1/8	125V 1-1/8A TYPE T PLUG FUSE
T-12	125V 12A TYPE T PLUG FUSE
T-14	125V 14A TYPE T PLUG FUSE
T-1-4/10	125V 1-4/10A TYPE T PLUG FUSE
T-15	125V 15A TYPE T PLUG FUSE
T-1-6/10	125V 1-6/10A TYPE T PLUG FUSE
T-1-8/10	125V 1-8/10A TYPE T PLUG FUSE
T-20	125V 20A TYPE T PLUG FUSE
T-2-1/4	125V 2-1/4A TYPE T PLUG FUSE
T-25	125V 25A TYPE T PLUG FUSE
T-3	125V 3A TYPE T PLUG FUSE
T-3/10	125V 3/10A TYPE T PLUG FUSE
T-30	125V 30A TYPE T PLUG FUSE
T-3-2/10	125V 3-2/10A TYPE T PLUG FUSE
T-4/10	125V 4/10A TYPE T PLUG FUSE
T-4-1/2	125V 4-1/2A TYPE T PLUG FUSE
T-5	125V 5A TYPE T PLUG FUSE
T-5-6/10	125V 5-6/10A TYPE T PLUG FUSE
T-6	125V 6A TYPE T PLUG FUSE
T-6/10	125V 6/10A TYPE T PLUG FUSE
T-6-1/4	125V 6-1/4A TYPE T PLUG FUSE
T-7	125V 7A TYPE T PLUG FUSE
T-8/10	125V 8/10A TYPE T PLUG FUSE
T-9	125V 9A TYPE T PLUG FUSE
TD15	125V 15A -D- PLUG FUSE
TD20	125V 20A -D- PLUG FUSE
TD25	125V 25A -D- PLUG FUSE
TD30	125V 30A -D- PLUG FUSE
TD15-2C	FUSE PLUG
TD20-2C	FUSE PLUG
TD25-2C	FUSE PLUG
TD30-2C	FUSE PLUG

© 2024 Mersen. All rights reserved. Mersen reserves the right to change, update, or correct, without notice, any information contained in this datasheet.