



T8 900 Series Rapid Start

F32T8/TL950 SLV

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data


General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T-8
Life to 50% Failures (Nom)	15,000 hour(s)		
Light Technical		Approval and Application	
Color Code	TL950 [CCT of 5000K (950)]	Mercury (Hg) Content (Nom)	5.0 mg
Luminous Flux	2,000 lm		
Luminous Efficacy (rated) (Nom)	63.9 lm/W	Product Data	
Color Designation	TL950	Order product name	F32T8/TL950 SLV
Correlated Color Temperature (Nom)	5000 K	Full product name	F32T8/TL950 SLV
Color rendering index (CRI)	98	Order code	927942009520
		Material Nr. (12NC)	927942009520
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	32 W	Net Weight (Piece)	137.500 g
Lamp Current (Nom)	0.265 A	EAN/UPC - Product/Case	046677209056
Wattage Equivalent	32 W	Numerator - Packs per outer box	25
Voltage (Nom)	139 V	EAN/UPC - Case	50046677209051
Controls and Dimming			
Dimmable	Yes		

T8 900 Series Rapid Start


Dimensional drawing

Product

F32T8/TL950 SLV



Photometric data



Spectral Power Distribution Colour - F32T8/TL950 SLV

