

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

LED HIGH INTENSITY FILAMENT LAMP

ORDERING INFORMATION

Order code: 70174
Model number: ED23.5/20W/30K/BYP/E26/V/FIL/ND/STD
UPC: 069549032347
Case quantity: 12

PHYSICAL DATA

Base: E26
Shape: ED23.5

PERFORMANCE DATA

Watts (W): 20
Traditional equivalent (W) 70
Volts (VAC): 120-277
Color temperature (K)¹: 3 000
Lumen output (lm)²: 3 500
Efficacy (lm/W): 175
CRI: 80
Life L70 (h)³: 25 000
Beam angle (°): Universal
Power factor: >0.9
Frequency (Hz): 50/60
Operating temp. range: Open Fixture: -30 °C to 50 °C (-22 °F to 122 °F)
Enclosed Fixture: -30 °C to 45 °C (-22 °F to 113 °F)
Indoor and Outdoor


Application (Indoor/Outdoor):

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

³ Life hours are derived from IESNA LM-80 testing report and projected per IESNA TM-21 extrapolations.

DIMENSIONS



3^{yrs}
warranty


**non
dimmable**


**enclosed
fixture**

66
**wet
location**


Intertek

FC

This lighting equipment meets requirements of ICES-005 issue 5 class B for use in residential applications.
Data is based upon tests performed in a controlled environment.
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.