

# Day-Brite

## CFI

by Signify

## Industrial

### Vaporlume LED DW

4' sealed industrial  
4300 to 7000 lm



Control options available

Day-Brite / CFI Vaporlume LED sealed industrial DW is a specialized wet location, IP rated product designed for use in both indoor and outdoor environments. It is a wet location listed, non-corrosive luminaire available in both fluorescent and LED light sources.

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lumens: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering guide

Example: DWAE51L840-4-UNV-MD360W

Family	Application	Lens	Hubs Installed	Lumen Package	Color Temp.	Length	Voltage	Driver	Options
<b>D</b>	<b>W</b>		<b>E</b>		-	-	-	-	
<b>D</b> Sealed industrial	<b>W</b> Wet Location	<b>A</b> DR Acrylic <b>P</b> Polycarbonate <b>L</b> Enhanced LED Acrylic	<b>E</b> Ends only	<b>35L</b> 3500 nominal lumens <b>43L</b> 4300 nominal lumens <b>51L</b> 5100 nominal lumens (25°C ambient) <b>51LH</b> 5100 nominal lumens (-35°C to 40°C) <b>70L</b> 7000 nominal lumens  Other lumen packages may be ordered in increments of 100lm up to 7000 lumens.	<b>830</b> 80 CRI, 3000K <b>835</b> 80 CRI, 3500K <b>840</b> 80 CRI, 4000K <b>850</b> 80 CRI, 5000K	<b>4</b> 4'	<b>UNV</b> Universal Voltage, 120-277V <b>347<sup>1</sup></b> 347V <b>480<sup>1</sup></b> 480V	<b>blank</b> <b>SDIM<sup>2</sup></b>	<b>0-10V</b> Step dimming to 40% input power  <b>MD360W<sup>3</sup></b> Wet location occupancy sensor, external <b>MD360WD<sup>3</sup></b> Wet location occupancy sensor, (ON/DIM to 10%) <b>WHP</b> Wide beam optic <b>EMLED<sup>3</sup></b> Integral emergency <b>IP67</b> Protection against effects of immersion <b>GLR</b> Fusing, fast blow <b>SWZCSH<sup>4</sup></b> Interact Pro scalable high bay sensor with integral daylight & occupancy sensing, advanced grouping with dwell time <b>SNH200<sup>4</sup></b> Integral EasySense occupancy & daylight sensor, with advanced SpaceWise type wireless grouping <b>SSL</b> Stainless steel latches

### Footnotes

- All 347V and 480V models available only for (-20°C to 25°C) ambient. Not available for use with 51LH or SDIM options.
- Step dim (SDIM) option not available on 51LH.
- EMLED option not available on 347V or 480V models.
- High bay motion detector. Motion sensing zone is extremely limited if used below 15' mounting height.
- Not available with SWZCSH or SNH200 option.

### Accessories (order separately)

- TBK** - Stainless Steel Top Bracket Kit (pair of brackets plus hardware)
- EBK** - Stainless Steel End Bracket Kit (pair of brackets plus hardware)
- WBK** - Stainless Steel Wraparound Bracket Kit (pair of brackets)
- FKR-126** - Chain Hanger Set (requires TBK)
- V2/DW-4ARL-CS** - 4' Acrylic Replacement Lens
- V2/DW-4PRL** - 4' Polycarbonate Replacement Lens
- V2/DW-4LRA** - 4' LED Frosted Acrylic Replacement Lens



interact ready.

# DW Vaporlume LED sealed industrial

4', 3500 to 7000 lumens

## Application

- Ideally suited for use in refrigerated cold storage, industrial, parking garage, and canopy applications.
- Acceptable for outdoor as well as indoor installations.
- Can be surface (wall/ceiling) or suspended mounted unless otherwise specified.
- Wet Location – Areas of high humidity, water vapor, rain, incidental water spray, or other non-corrosive or nonflammable liquid.
- Excellent for applications such as garages, stairwells, storage areas, horizontal shelf-mount refrigerated cases, and cold storage.
- Mounting brackets available, order separately.
- IP65 rating standard. IP67 configuration available.
- LED sources provide excellent low temperature performance. This product can replace a fluorescent model in cold environments with significant energy savings.
- 51LH model listed for use in -35°C to 40°C ambient. 50,000 hour L70 lumen maintenance.
- 35L/43L models listed for use in -20°C to 40°C ambient. 100,000 hour L70 lumen maintenance.
- 51L/70L models listed for use in -20°C to 25°C ambient. L70 lumen maintenance is 100,000 hours for 51L model, and 50,000 hours for 70L.
- NSF Certified for Non-Food Zone Installations.
- EMLLED 1100lm nominal in DC mode
- WHP wide optic is an acrylic lens factory installed on the LED arrays, provides compliance to DLC requirements for parking garage luminaires

## Construction/Finish

- Non-conductive, non-corrosive housing.
- Smooth exterior surface for easy cleaning.
- White one piece, molded fiberglass reinforced polyester body. No rusting, no oxidation, and no corrosion.
- Standard acrylic lens (A) is stippled sheet of .130" nominal thickness.
- Optional LED lens (L) designed specifically to further reduce pixilated glare from LED's. Linear rib profile.
- Optional polycarbonate lens (P) will not be yellowed by LED sources because they do not produce UV.

- Continuous compressible closed cell gasket provides tight seal between plastic enclosure and luminaire body.
- White ABS cam action latches standard.
- Pre-painted steel lighting channel.
- Two gasketed threaded (½" trade size) wet location hubs installed on ends.

## Electrical

- High efficiency LEDs provide up to 100,000 hour rated life (L70, defined as 70% lumen maintenance @ rated maximum ambient).
- Dimming to 5% on 0-10V controls standard. Step dim (SDIM) option available, 100/40% levels.
- Driver and LED boards are accessible from below. LED boards are individually replaceable if required.
- Combinations are available providing as much as 117 delivered lumens per Watt.
- Nominal lumen packages range from 3,500 to 7,000 lumens, providing flexibility to optimize light levels for a specific application.
- LED sources provide full illumination in low temperature applications, unlike fluorescent sources that provide reduced light levels in very cold environments.
- LED sources can be frequently switched with no negative impact on life.
- Minimum 80 CRI provides smooth color rendering that rivals or exceeds performance of fluorescent lamps.
- Light output from the luminaire contains no infrared or ultraviolet energy, so the light won't heat or fade the objects being lit.
- Available motion sensor further increases energy savings in areas where occupancy is not continuous.

## Labels

- cETLus listed to UL 1598. Suitable for use in wet locations.
- 5 Year Limited Warranty, [www.signify.com/warranties](http://www.signify.com/warranties)
- Certain luminaire components may be adversely affected by contaminants. If sulfur, chlorine, or petroleum based solutions, or other contaminants will be in the area of operation, please consult factory as damage caused by these contaminants are not covered under our limited warranty.

## Interact Pro scalable sensor for Foundation, Advanced & Enterprise tiers (SWZCSH and an evolution of SpaceWise)

- SWZCSH is a connected sensor with integral occupancy and daylight sensing and supports wireless mesh connectivity.

- The sensor works in the Foundation mode (similar to SpaceWise) when configured without a gateway or in an Interact Pro Advanced or Enterprise mode if a compatible gateway is used.
- Interact Pro includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & BlueTooth connectivity. The App provides flexibility to choose between a gateway or non gateway mode for setup.

- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely and use IRT9015 remote

onsite to identify and group devices together.

- Compatible with:

- UID8451/10 wireless dimmer switch

- SWS200 wireless scene switch

- Battery powered IP42 presence sensor OCC sensor IA CM WH 10/1

- Battery powered IP42 presence & daylight sensor OCC-DL sensor IA CM IP42 WH

- LCN3110/05 battery powered IP65 presence sensor OCC sensor IA CM IP65 WH

- LCN3120/05 battery powered IP65 presence & daylight sensor OCC-DL sensor IA CM IP65 WH

- For more information on Interact Pro visit: [www.interact-lighting.com/interactproscalablesystem](http://www.interact-lighting.com/interactproscalablesystem)

## SNH200 EasySense

- Philips field apps allow programming of occupancy & daylight sensing parameters and fine-tuning of light levels during installation. It can also be used for grouping of fixtures.
- Download "Philips field apps" from the Google Play Store.
- Register for the commissioning app at <http://registration.componentcloud.philips.com/appregistration/>.
- The app works on certain Android phones with NFC or IR. See Recommended Phones and the EasySense App User Manual in the download section at <http://www.usa.lighting.philips.com/products/lighting-components/easysense> and follow the "View Downloads" link to register for access to the download area. Navigate to Connected-Lighting-Components and then Philips-EasySense-Sensors to find downloads.

# DW Vaporlume LED sealed industrial


4', 3500 to 7000 lumens

Interact Pro scalable system			
	Foundation	Advanced	Enterprise
Dimming, grouping, and zoning	✓	✓	✓
Bluetooth and ZigBee enabled	✓	✓	✓
Motion sensing and daylight harvesting	✓	✓	✓
Integration with 0-10V and phase dimming fixtures	✓	✓	✓
Code compliance	✓	✓	✓
Granular dimming and dwell time	✓	✓	✓
Energy reporting and monitoring		✓	✓
Scheduling		✓	✓
Demand response		✓	✓
BMS integration (BACnet)			✓
Floor plan visualization			✓
IoT sensors for wellness			✓
IoT Apps for productivity			✓

## Currently supported maximum system size

To be able to design the lighting system correctly for the customer, it is important to know the prime characteristics of the system, its possibilities and limitations.



System level	
Total number of gateways	Unlimited
Total number of devices	200 per network
• luminaires with integrated sensors	150
• smart TLEDS	150
Total number of ZGP devices (sensors and switches)	50
• sensors	30
• switches	50
• zones and groups	64
Group level	
Recommended number of lights	40 (recommended 25)
Number of ZGP devices	5
Number of scenes	16




# DW Vaporlume LED sealed industrial

4', 3500 to 7000 lumens

## Dimensions




Shallow acrylic (A) and polycarbonate (P) lens




Enhanced LED acrylic lens (L)

## Mounting Brackets


### TBK - Top Mounting Bracket




### EBK - End Mounting Bracket




### WBK - Wraparound Mounting Bracket




### EBK - End Mounting Bracket



Acrylic Lens



Polycarbonate Lens



LED Frosted Acrylic Lens

# DW Vaporlume LED sealed industrial

4', 3500 to 7000 lumens

## 4' Vaporlume LED DW, 3500 nominal lumens

## LER-117

Catalog No.	DWAE35L840-4	Candlepower				
		Angle	End	45	Cross	Back-45
Test No.	32643	0	1250	1250	1250	1250
S/MH	1.2	5	1244	1239	1243	1239
Source	LED	15	1204	1201	1199	1201
Input Watts	32	25	1112	1114	1106	1114
Delivered Lumens	3699	35	966	964	949	964
		45	778	777	841	777
		55	576	685	708	685
		65	371	509	472	509
		75	193	250	271	250
		85	49	91	96	91
		95	19	36	28	36
		105	17	30	20	30
		115	10	28	20	28
		125	4	19	19	19
		135	2	10	17	10
		145	1	3	9	3
		155	1	1	2	1
		165	1	1	1	1
		175	1	1	1	1

Comparative yearly lighting energy cost per 1000 lumens – \$2.03 based on 3000 hrs. and \$.08 pwr KWH.

Photometric values based upon tests performed in compliance with LM-79.

### Coefficients of Utilization

#### EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)

pcc	80				70				50			
	pw	70	50	30	70	50	30	70	50	30	50	30
RCR												
0	117	117	117		114	114	114		110	110		
1	108	103	97		105	100	95		94	92		
2	97	89	81		94	86	80		82	77		
3	89	78	69		85	76	68		72	66		
4	81	68	59		79	68	58		65	56		
5	75	61	53		71	59	52		57	50		
6	68	55	46		67	54	46		52	45		
7	64	50	40		61	48	40		46	40		
8	58	46	36		57	45	36		42	35		
9	56	41	34		54	40	33		40	33		
10	52	39	30		51	38	30		36	29		

### Light Distribution

Degrees	Lumens	% Luminaire
0-30	969	26.1
0-40	1569	42.3
0-60	2772	74.8
0-90	3602	97.1
90-120	81	2.2
90-130	95	2.6
90-150	105	2.8
90-180	106	2.9
0-180	3708	100.0

### Average Luminance

Angle	End	45'	Cross
45	5069	4222	4360
55	4543	4228	4105
65	865	3770	3222
75	3096	2402	2333
85	1821	1312	1164

## 4' Vaporlume LED DW, 4300 nominal lumens

## LER-116

Catalog No.	DWAE43L840-4	Candlepower				
		Angle	End	45	Cross	Back-45
Test No.	32642	0	1496	1496	1496	1496
S/MH	1.2	5	1491	1487	1485	1487
Source	LED	15	1443	1439	1441	1439
Input Watts	38	25	1332	1338	1323	1338
Delivered Lumens	4431	35	1158	1151	1132	1151
		45	933	926	1000	926
		55	688	819	854	819
		65	444	611	566	611
		75	231	300	324	300
		85	58	110	118	110
		95	23	43	35	43
		105	20	36	25	36
		115	12	34	24	34
		125	5	24	24	24
		135	3	12	21	12
		145	2	4	11	4
		155	1	1	3	1
		165	1	1	1	1
		175	1	1	1	1

Comparative yearly lighting energy cost per 1000 lumens – \$2.07 based on 3000 hrs. and \$.08 pwr KWH.

Photometric values based upon tests performed in compliance with LM-79.

### Coefficients of Utilization

#### EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)

pcc	80				70				50			
	pw	70	50	30	70	50	30	70	50	30	50	30
RCR												
0	117	117	117		114	114	114		109	109		
1	108	103	97		104	100	95		94	92		
2	97	89	81		94	86	80		82	77		
3	89	78	69		85	76	68		72	66		
4	81	68	59		79	67	58		65	56		
5	75	61	53		71	59	52		57	50		
6	68	55	46		67	54	46		52	45		
7	64	50	40		61	48	40		46	40		
8	58	46	36		57	45	36		42	35		
9	56	41	34		54	40	33		40	33		
10	52	39	30		51	38	30		36	29		

### Light Distribution

Degrees	Lumens	% Luminaire
0-30	1161	26.1
0-40	1880	42.3
0-60	3318	74.7
0-90	4313	97.1
90-120	99	2.2
90-130	116	2.6
90-150	128	2.9
90-180	129	2.9
0-180	4442	100.0

### Average Luminance

Angle	End	45'	Cross
45	6078	5034	5182
55	5434	5059	4955
65	4626	4531	3867
75	3704	2883	2786
85	2173	1578	1433

# DW Vaporlume LED sealed industrial

4', 3500 to 7000 lumens

## 4' Vaporlume LED DW, 5100 nominal lumens LER-111

		Candlepower				
Catalog No.	DWAE51L840-4	Angle	End	45	Cross	Back-45
Test No.	32640	0	1729	1729	1729	1729
S/MH	1.2	5	1722	1716	1709	1716
Source	LED	15	1666	1651	1632	1651
Input Watts	46	25	1542	1523	1494	1523
Delivered Lumens	5129	35	1340	1307	1250	1307
		45	1091	1039	1117	1039
		55	817	909	884	909
		65	533	670	574	670
		75	280	309	286	309
		85	75	107	86	107
		95	26	47	34	47
		105	24	42	30	42
		115	14	39	29	39
		125	6	28	28	28
		135	4	16	24	16
		145	3	5	12	5
		155	2	2	3	2
		165	2	2	2	2
		175	2	2	2	2

Comparative yearly lighting energy cost per 1000 lumens – \$2.16 based on 3000 hrs. and \$.08 pwr KWH.

Photometric values based upon tests performed in compliance with LM-79.

### Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)									
pcc	80			70			50		
	pw	70	50	30	70	50	30	50	30
RCR									
0	117	117	117	114	114	114	110	110	
1	108	103	97	104	100	95	94	92	
2	97	89	81	94	86	80	82	77	
3	89	78	69	85	76	68	72	66	
4	81	68	59	79	68	58	65	56	
5	75	61	53	71	59	52	57	50	
6	68	55	46	67	54	46	52	45	
7	64	50	40	61	48	40	46	40	
8	58	46	36	57	45	36	42	35	
9	56	41	34	54	40	33	40	33	
10	52	39	30	51	38	30	36	29	

### Light Distribution

Degrees	Lumens	% Luminaire
0-30	1344	26.1
0-40	2176	42.3
0-60	3842	74.7
0-90	4992	97.1
90-120	114	2.2
90-130	133	2.6
90-150	148	2.9
90-180	149	2.9
0-180	5141	100.0

### Average Luminance

Angle	End	45°	Cross
45	7103	5648	5790
55	6447	5616	5126
65	5552	4964	3915
75	4486	2974	2465
85	2784	1530	1043

## 4' Vaporlume LED DW, 7000 nominal lumens LER-107

		Candlepower				
Catalog No.	DWAE70L840-4	Angle	End	45	Cross	Back-45
Test No.	32614	0	2357	2357	2357	2357
S/MH	1.2	5	2351	2342	2345	2342
Source	LED	15	2274	2271	2270	2271
Input Watts	65	25	2101	2105	2089	2105
Delivered Lumens	6985	35	1818	1814	1784	1814
		45	1467	1462	1586	1462
		55	1085	1302	1345	1302
		65	701	959	891	959
		75	365	469	503	469
		85	92	170	176	170
		95	36	67	53	67
		105	33	57	39	57
		115	19	53	39	53
		125	8	38	38	38
		135	4	20	33	20
		145	3	6	18	6
		155	2	2	4	2
		165	2	2	2	2
		175	2	2	2	2

Comparative yearly lighting energy cost per 1000 lumens – \$2.24 based on 3000 hrs. and \$.08 pwr KWH.

Photometric values based upon tests performed in compliance with LM-79.

### Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)									
pcc	80			70			50		
	pw	70	50	30	70	50	30	50	30
RCR									
0	117	117	117	114	114	114	109	109	
1	108	103	97	105	100	95	94	92	
2	97	89	81	94	86	80	82	77	
3	89	78	69	85	76	68	72	66	
4	81	68	59	79	67	58	65	56	
5	75	61	52	71	59	52	57	50	
6	68	55	46	67	54	46	52	45	
7	64	50	40	61	48	40	46	40	
8	58	46	36	57	45	36	42	35	
9	56	41	34	54	40	33	40	33	
10	52	39	30	51	38	30	36	29	

### Light Distribution

Degrees	Lumens	% Luminaire
0-30	1830	26.1
0-40	2961	42.3
0-60	5230	74.7
0-90	6798	97.1
90-120	156	2.2
90-130	183	2.6
90-150	203	2.9
90-180	205	2.9
0-180	7003	100.0

### Average Luminance


Angle	End	45°	Cross
45	9554	7946	8219
55	8566	8043	7802
65	7304	7108	6080
75	5848	4516	4329
85	3444	2433	2142

# DW Vaporlume LED sealed industrial


4', 3500 to 7000 lumens

## Energy Data


Model	Initial Delivered Lumens @ 25°C Ambient	Input Power	Lumens per Watt	Application notes
DWAE35L840-4-UNV	3,699	32W	117 LPW	<ul style="list-style-type: none"> <li>Slightly less than 2 lamp F32T8 at room temperature, 35% energy savings.</li> <li>Equivalent to 2 lamp F32T8 in refrigerator (40°F), 35% energy savings.</li> </ul>
DWAE43L840-4-UNV	4,431	38W	116 LPW	<ul style="list-style-type: none"> <li>Equivalent to 2 lamp F32T8 at room temperature, 15% energy savings.</li> <li>Double the output of 2 lamp F32T8 in freezer (25°F) at the SAME energy use.</li> </ul>
DWAE51L840-4-UNV	5,129	46W	111 LPW	<ul style="list-style-type: none"> <li>Equivalent to high ballast factor 2 lamp F32T8 at room temperature, 15% energy savings.</li> </ul>
DWAE70L840-4-UNV	6,985	65W	107 LPW	<ul style="list-style-type: none"> <li>Equivalent to 3 lamp F32T8 at room temperature, 30% energy savings.</li> </ul>



— 2-LAMP F32T8 — DWAE35L840 — DWAE43L840  
 — DWAE51L840 — DWAE70L840



— 2-LAMP F32T8 — DWAE35L840 — DWAE43L840  
 — DWAE51L840 — DWAE70L840



— 2-LAMP F32T8 — DWAE35L840 — DWAE43L840  
 — DWAE51L840 — DWAE70L840

