



PRODUCT-DETAILS

ACS880-01-034A-5

LV AC industrial wall-mounted single drive, IEC:  
Pn 18.5 kW, 34 A, 500 V, UL: Pld 25 Hp, 34 A,  
460 V (ACS880-01-034A-5)



General Information	
Global Commercial Alias	ACS880-01-034A-5
Product ID	3AUA0000090437
ABB Type Designation	ACS880-01-034A-5
EAN	6438177557418
Catalog Description	LV AC industrial wall-mounted single drive, IEC: Pn 18.5 kW, 34 A, 500 V, UL: Pld 25 Hp, 34 A, 460 V (ACS880-01-034A-5)
Long Description	<p>The ACS880-01 drives are customized to meet the particular needs of specific industries, such as oil and gas, mining, metals, chemicals, cement, power plants, material handling, pulp and paper, sawmills, marine, water and wastewater, food and beverage, and automotive. They can control a wide range of applications, including cranes, extruders, winches, winders, conveyors, mixers, compressors, centrifuges, test benches, elevators, extruders, pumps and fans.</p> <p>The ACS880-01 comes in one compact package for easy installation and commissioning. The drive can be installed on the wall as standard and in a cabinet as an option. The drive offering includes enclosure classes up to IP55, making it suitable for most environments and installations. ACS880-01 drives have all the essential features built-in. These features include as standard a choke for harmonic filtering as well as options like a brake chopper, EMC filter and communication protocol adapter, functional safety, external output filters and I/O extension modules.</p>

Ordering

Customs Tariff Number	85044086
HS Code	850440-- Electrical transformers, static converters (for example, rectifiers) and inductors.- Static converters
Invoice Description	ACS880-01-034A-5 PN: 18.5 kW, IN: 34 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

## Dimensions

Product Net Weight	10.8 kg 23.810 lb
Product Net Depth / Length	261 mm 10.276 in
Product Net Height	475 mm 18.701 in
Product Net Width	173 mm 6.81 in
Package Level 1 Depth / Length	624 mm 24.57 in
Package Level 1 Height	316 mm 12.441 in
Package Level 1 Width	256 mm 10.079 in
Package Level 1 Units	1 carton

## Certificates and Declarations

Declaration of Conformity - CE	3AXD10000497831
REACH Date	20241203
REACH Declaration	9AKK107992A7060
REACH Information	True - contains substances > 0.1 mass percentage
RoHS Date	20240508
RoHS Information	3AXD10000497831
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

## Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Altitude	4000 m 5 ... 95
Sound dB (A)	60 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 2 pcs, 6 g
Frequency (f)	47.5 ... 63 Hz
Frame Size	R3
Input Voltage ( $U_{in}$ )	380 ... 500 V
Mounting Type	Wall-mounted
Communication Protocol	CAN DeviceNet EtherNet/IP MODBUS Other Bus Systems PROFIsafe PROFIBUS PROFINET IO

Number of Hardware Interfaces	Industrial Ethernet 0 Other 4 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 2
Output Current, Normal Use ( $I_N$ )	34 A
Output Current, Light-Overload Use ( $I_{LD}$ )	32 A
Output Current, Heavy-Duty Use ( $I_{HD}$ )	27 A
Output Power, Normal Use ( $P_N$ )	18.5 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	18.5 kW
Output Power, Heavy-Duty Use ( $P_{HD}$ )	15.0 kW
	454 W
Apparent Power Output	29 kV·A
Efficiency Level	IE2
Standby Loss	27 W
Complete Drive Module Efficiency (IEC61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	166 W	0.6 %	90.4 %
0 / 50 %	218 W	0.7 %	93.3 %
0 / 100 %	344 W	1.2 %	94.6 %
50 / 25 %	172 W	0.6 %	95.0 %
50 / 50 %	233 W	0.8 %	96.4 %
50 / 100 %	393 W	1.3 %	97.0 %
90 / 50 %	255 W	0.9 %	97.8 %
90 / 100 %	454 W	1.5 %	98.0 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

## Technical UL

Output Current, Heavy-Duty Use (UL)	27 A
Output Current, Light-Overload Use (UL)	34 A
Output Current, Normal Use (UL)	- A
Output Power, Heavy-Duty Use (UL)	20 Hp
Output Power, Light-Overload Use (UL)	25 Hp

External Classifications and Standards	
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental	
SCIP	4ac5f0da-ba5c-4c9a-bfbf-279008b38a92 Finland
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Industrial Drives → ACS880 Single Drives → ACS880-01 - Wall-mounted single drive

