

Project: _____

Type: _____

Drawn by: _____ Catalogue #: _____

Date: _____

Individual Spec Sheet

LED REFLECTORS

CHOICE

GU10

ORDERING INFORMATION

Order code: 70262
 Model number: GU10/S3/7W/30K/40/CHOICE/STD
 UPC: 069549033306
 Case quantity: 24

PHYSICAL DATA


Dimensions: MOL: 55.7 mm (2 1/4")
 DIA: 50 mm (1 32/32")
 Shape: MR16
 Base: GU10
 Finish: Lens: Frosted

PERFORMANCE DATA

Watts (W):	7	Beam angle (°):	40°
Traditional equivalent (W):	50	CBCP (cd):	976
Volts (V AC/DC):	120	Power factor:	0.7
Color temperature (K) ¹ :	3 000	Input Current (mA):	77
Lumen output (lm) ² :	500	Frequency (Hz):	60
Efficacy (lm/W):	70	Lens material:	Plastic
CRI:	80	Housing Material:	Aluminum, Plastic
Dimmable	Yes	Application:	Indoor
Life L70 (h) ³ :	25 000	Operating temp. range:	-40 °C / -40 °F to 45 °C / 113 °F

¹ Typical colour temperature range: +/- 5 %.² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.³ Life hours are derived from IESNA LM-80 testing report and projected per IESNA TM-21 extrapolations.

DIMENSIONS

COMPATIBLE DIMMERS¹

Brand	Model
LUTRON	HCL453P*, PD-6WCL, MDVCL-153P, CTCL-153P, DVCL-253P*, AYCL-253P, MACL-153P
COOPER	SAL06P3
LEVITON	IPL06*, DSM10-1LZ, DDMX1
LEGRAND	RH730PTUTC*

* Flickering may occur on low intensity.

¹ This table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Some dimmers may require more than one product for stable operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation.

Dimming performance might be impacted when using the above dimmers with only one lamp. Full performance achieved when using two or more lamps.



3^{yrs}
 warranty



dimmable

damp
locationenclosed
fixtureICES
005