

Data Sheet | Item Number: 750-564

4-channel analog output; Voltage/Current

<https://www.wago.com/750-564>



The analog output module provides a variety of standardized signals for voltage and current. The output signal can be parameterized channel by channel. The output signal is electrically isolated and transmitted with a resolution of 16 bits. Both the internal system and field side supply power the module. Wire break, overload and insufficient field supply, are diagnosed and displayed.

The module is protected against wrong wiring (feedback).

Voltage outputs can optionally be connected in 4-wire technology via the sense lines.

The module can be configured via GSD file, *e!COCKPIT* and *WAGO-I/O-CHECK*.

Technical data

Number of analog outputs	4
Total number of channels (module)	4
Signal type	Voltage Current
Signal type (current)	0 ... 10 mA; 2 ... 10 mA; -10 ... +10 mA; 0 ... 20 mA; 4 ... 20 mA; -20 ... +20 mA; 0 ... 22 mA; -22 ... +22 mA; 0 ... 12 mA; -12 ... +12 mA
Signal type (voltage)	0 ... 5 V; 1 ... 5 V; -5 ... +5 V; 0 ... 10 V; 2 ... 10 V; -10 ... +10 V; 0 ... 12 V; -12 ... +12 V
Actuator connection	4 x (2-wire); Voltage outputs can optionally be connected in 4-wire technology via the sense lines.
Resolution [bit]	16 bits
Data width	4 x 16-bit data; 4 x 8-bit control/status (optional)
Load impedance (voltage output)	≥ 1 kΩ
Load impedance (current output)	≤ 600 Ω
Conversion time (typ.)	3 ms
Reference for measurement error	Voltage/current
Output error, reference temperature	25 °C
Output error, deviation (max.) of the upper-range value	0.05 %
Temperature coefficient	U: ±25 ppm/K of the upper-range value; I: ±50 ppm/K of the upper-range value
Configuration options	<i>WAGO-I/O-CHECK</i> CODESYS Library <i>e!COCKPIT</i>
Supply voltage (system)	5 VDC; via data contacts
Current consumption (5 V system supply)	55 mA
Supply voltage (field)	24 VDC (-25 ... +30 %); via power jumper contacts (power supply via blade contact; transmission (supply voltage field side only) via spring contact)
Isolation	500 V system/field
Indicators	LED (1-4) green: Status AO 1 ... AO 4; LED (9-12) red: Error AO 1 ... AO 4
Number of incoming power jumper contacts	2
Number of outgoing power jumper contacts	2

Connection data

Connection technology: inputs/outputs	16 x Push-in CAGE CLAMP®
Connection type 1	Inputs/outputs
Solid conductor	0.08 ... 1.5 mm ² / 28 ... 16 AWG
Fine-stranded conductor	0.25 ... 1.5 mm ² / 22 ... 16 AWG
Strip length	8 ... 9 mm / 0,31 ... 0.35 inches

Physical data

Width	12 mm / 0.472 inches
Height	100 mm / 3.937 inches
Depth	69 mm / 2.717 inches
Depth from upper-edge of DIN-rail	61.8 mm / 2.433 inches

Mechanical data

Mounting type	DIN-35 rail
---------------	-------------

Material data

Housing material	Polycarbonate; polyamide 6.6
Fire load	0.848 MJ
Weight	51 g
Conformity marking	CE

Environmental requirements

Ambient temperature (operation)	0 ... +55 °C
Ambient temperature (storage)	-40 ... +85 °C
Protection type	IP20
Pollution degree	2 per IEC 61131-2
Operating altitude	0 ... 2000 m / 0 ... 6562 ft
Mounting position	Horizontal left, horizontal right, horizontal up, horizontal down, vertical top and vertical bottom
Relative humidity (without condensation)	95 %
Shock resistance	15g per IEC 60068-2-27
EMC immunity to interference	per EN 61000-6-2
EMC emission of interference	per EN 61000-6-3
Exposure to pollutants	per IEC 60068-2-42 and IEC 60068-2-43
Permissible H ₂ S contaminant concentration at a relative humidity 75 %	10 ppm
Permissible SO ₂ contaminant concentration at a relative humidity 75 %	25 ppm

Commercial data

ETIM 9.0	EC001596
ETIM 8.0	EC001596
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143933223
Customs tariff number	85389099990

Environmental Product Compliance

CAS-No.	1303-86-2 1317-36-8 7439-92-1
REACH Candidate List Substance	Diboron trioxide Lead Lead monoxide
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c) 7(a) 7(c)-I 7(c)-II
SCIP notification number (Austria)	ff605b72-1492-4eea-9540-1b10a4e14799
SCIP notification number (Belgium)	6a38898c-c23c-4020-892c-9d000e0e599d
SCIP notification number (Bulgaria)	76060568-a696-456c-8df1-15068ddae193

Environmental Product Compliance

SCIP notification number (Czech Republic)	ef4e81d6-7c41-48d8-85eb-cbf0c1342f1e
SCIP notification number (Denmark)	439e8787-5feb-4a13-8c47-0f47a5c15fe3
SCIP notification number (Finland)	3b28c00f-c0c3-42e2-9c8a-5aaadb1d3175
SCIP notification number (France)	eb5c9baa-4301-427c-a15f-be6b86254555
SCIP notification number (Germany)	752bd75f-a999-4db8-a314-d67481047d66
SCIP notification number (Hungary)	4808eb04-de68-43cb-9240-bfde84ecb644
SCIP notification number (Italy)	e4d68597-2633-42ac-9cd6-838d61cebad8
SCIP notification number (Netherlands)	298d87f9-e91b-4799-bce6-dfda9d0e0c0b
SCIP notification number (Poland)	4fe1d60a-ced7-4c3c-b0cd-8f8b9a7f5631
SCIP notification number (Romania)	19c7ac7f-1b97-4342-b605-787060b72971
SCIP notification number (Sweden)	bf2e9e26-969f-427b-9740-ce4e3fda6797