


## Data Sheet | Item Number: 811-1316

2-conductor fuse holder ; with pivoting fuse holder; with test option; for cylindrical fuses 10/14 x 85 mm; for photovoltaic applications; 1-pole; 1500 VDC; for DIN-rail 35 x 15 and 35 x 7.5; 16 mm<sup>2</sup>; CAGE CLAMP®; 16,00 mm<sup>2</sup>; light gray

<https://www.wago.com/811-1316>



Color: ■ light gray





Our fuse terminal block (item number 811-1316) simplifies electrical installations. Strip lengths must be between 12 mm and 13 mm when connecting conductors to this fuse terminal block. Featuring conductor terminals along with CAGE CLAMP®, this connector is highly versatile. Our CAGE CLAMP® connection provides a safe and maintenance-free way to connect all types of conductors. You do not need to prepare the conductor in any way, such as crimping ferrules. Depending on the conductor type, this fuse terminal block is suitable for conductor cross sections ranging from 2.5 mm² to 16 mm². Up to one potential / one pole can be connected to this terminal block using two clamping points on one level. The light gray housing is made of polyamide (PA66) for insulation. These function terminal blocks are mounted using DIN-35 rails..

## Safety Information

The fuse holder must not be opened under load.

## Safety information 2

Do not cover the ventilation openings.