




GSC752N30B5H - Safety Ground Stud, Tin Plated Cast Copper, Inline NEMA Pad, 30 mm ball stud, Grade 5H

By Burndy
Catalog # [GSC752N30B5H](#)



Used when servicing a pad mounted transformer, our ground studs have an optional thermoplastic elastomer cover providing safe maintenance of equipment for optimal uptime for your upcoming projects in the Renewable, Industrial, and Utility Markets.

Features

- 30mm Ball Stud
- Inline pad
- NEMA spacing for 1/2" Hardware
- Cast copper alloy
- Tin-plated for corrosion resistance
- Stud Cover Available - GSC75030BCOVER

General

Catalog Number	GSC752N30B5H
Material	Tin-Plated Copper
Size	30mm Ball Stud
Type	Safety Ground Stud
UPC	621945651081

Dimensions

Dimensions	8.73 in x 1.25 in x 1.50 in
Height	1.5 in
Length	8.73 in
Width	1.25 in

Logistics

Carton Quantity	100
Pallet Quantity	1000

Product Assets

- [Catalog Page - BURNDY Master Catalog Page E-75](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sell Sheets - Temporary Protective Ground Studs](#)



A Hubbell brand