

BA | BELLA™

HIGH-END BASEBOARD



LA DOLCE VITA WITH BELLA

The high-end Bella baseboard is undoubtedly the most beautiful offered on the market. Its breathtaking design and sturdy aluminum-extruded facade make it the ideal choice for residential and commercial locations. The Bella is available in two densities: 150 W or 250 W per linear foot.

- **CLEAN AND HIGH-END FINISH**
- **EXTREMELY SOLID, IMPACT AND RUST RESISTANT**
MADE OF EXTRUDED ALUMINUM
- **FIT FOR RESIDENTIAL AND COMMERCIAL ENVIRONMENTS**
- **TOTALLY QUIET**

COLOURS

- **standard:** white
- **Orora (optional):** refer to www.stelpro.com/en-CA/Orora

FINISH

- epoxy-polyester powdercoat

MANUFACTURING

- 22-gauge steel cabinet
- 11-gauge equivalent extruded aluminum with molded and curved end-caps
- discreet air inlet: air enters through the front of the unit and exits from the top
- thermal protection with automatic reset
- full-length wireway

ELEMENT

- single tubular, stainless steel sheathed element with boxed aluminum fins for improved heat dissipation; the element is securely fastened at its centre, floating in nylon sleeves at each end, eliminating expansion and contraction noises

CONTROL

- wall thermostat (not included) – the use of an electronic thermostat is strongly recommended
- built-in mechanical single pole or double pole thermostat, installed in the left or right junction box (optional)
- low voltage relay kit installed in the left or right junction box (optional)
- disconnect switch (optional)

INSTALLATION

- surface mounted
- wiring compartment at both ends of unit

WARRANTY

- five years, *lifetime warranty on the heating element (for original owner)

IDEAL FOR:

kitchen, living room, bedroom, basement, commercial space, office

TECHNICAL SPECIFICATIONS

DENSITY OF 250 W PER LINEAR FOOT		DENSITY OF 150 W PER LINEAR FOOT			VOLTAGE	TOTAL LENGTH		WALL LENGTH		WEIGHT	
CODE	WATTS	CODE	WATTS		VOLTS	MM	IN.	MM	IN.	KG	LB
BA03019	300	---	---		120	597	23 1/2	584	23	2.5	5.5
BA03089	300	---	---		208	597	23 1/2	584	23	2.5	5.5
BA03029	300/225	---	---		240/208	597	23 1/2	584	23	2.5	5.5
---	300	---	---		347	597	23 1/2	584	23	2.5	5.5
---	300	---	---		600	597	23 1/2	584	23	2.5	5.5
BA0501	500	BAL0301	300		120	732	28 13/16	719	28 5/16	3.0	6.5
BA0508	500	BAL0308	300		208	732	28 13/16	719	28 5/16	3.0	6.5
BA0502	500/375	BAL0302	300/225		240/208	732	28 13/16	719	28 5/16	3.0	6.5
BA0503	500	---	300		347	732	28 13/16	719	28 5/16	3.0	6.5
---	500	---	300		600	732	28 13/16	719	28 5/16	3.0	6.5
BA0751	750	BAL0451	450		120	978	38 1/2	965	38	3.6	8.0
BA0758	750	BAL0458	450		208	978	38 1/2	965	38	3.6	8.0
BA0752	750/560	BAL0452	450/340		240/208	978	38 1/2	965	38	3.6	8.0
BA0753	750	BAL0453	450		347	978	38 1/2	965	38	3.6	8.0
BA0756	750	---	450		600	978	38 1/2	965	38	3.6	8.0
BA1001	1000	BAL0601	600		120	1229	48 3/8	1216	47 7/8	4.4	9.7
BA1008	1000	BAL0608	600		208	1229	48 3/8	1216	47 7/8	4.4	9.7
BA1002	1000/750	BAL0602	600/450		240/208	1229	48 3/8	1216	47 7/8	4.4	9.7
BA1003	1000	BAL0603	600		347	1229	48 3/8	1216	47 7/8	4.4	9.7
BA1006	1000	---	600		600	1229	48 3/8	1216	47 7/8	4.4	9.7
BA1251	1250	BAL0751	750		120	1478	58 3/16	1465	57 11/16	5.2	11.4
BA1258	1250	BAL0758	750		208	1478	58 3/16	1465	57 11/16	5.2	11.4
BA1252	1250/940	BAL0752	750/560		240/208	1478	58 3/16	1465	57 11/16	5.2	11.4
BA1253	1250	BAL0753	750		347	1478	58 3/16	1465	57 11/16	5.2	11.4
BA1256	1250	BAL0756	750		600	1478	58 3/16	1465	57 11/16	5.2	11.4
BA1501	1500	BAL0901	900		120	1707	67 3/16	1694	66 11/16	6.0	13.2
BA1508	1500	BAL0908	900		208	1707	67 3/16	1694	66 11/16	6.0	13.2
BA1502	1500/1125	BAL0902	900/675		240/208	1707	67 3/16	1694	66 11/16	6.0	13.2
BA1503	1500	BAL0903	900		347	1707	67 3/16	1694	66 11/16	6.0	13.2
BA1506	1500	BAL0906	900		600	1707	67 3/16	1694	66 11/16	6.0	13.2
---	1750	BAL1051	1050		120	1953	76 7/8	1940	76 3/8	6.8	15.0
BA1758	1750	BAL1058	1050		208	1953	76 7/8	1940	76 3/8	6.8	15.0
BA1752	1750/1310	BAL1052	1050/790		240/208	1953	76 7/8	1940	76 3/8	6.8	15.0
BA1753	1750	BAL1053	1050		347	1953	76 7/8	1940	76 3/8	6.8	15.0
BA1756	1750	BAL1056	1050		600	1953	76 7/8	1940	76 3/8	6.8	15.0
---	2000	BAL1201	1200		120	2154	84 13/16	2141	84 5/16	7.7	16.9
BA2008	2000	BAL1208	1200		208	2154	84 13/16	2141	84 5/16	7.7	16.9
BA2002	2000/1500	BAL1202	1200/900		240/208	2154	84 13/16	2141	84 5/16	7.7	16.9
BA2003	2000	BAL1203	1200		347	2154	84 13/16	2141	84 5/16	7.7	16.9
BA2006	2000	BAL1206	1200		600	2154	84 13/16	2141	84 5/16	7.7	16.9
---	2250	---	1350		120	2405	94 11/16	2392	94 3/16	8.6	18.8
BA2258	2250	BAL1358	1350		208	2405	94 11/16	2392	94 3/16	8.6	18.8
BA2252	2250/1690	BAL1352	1350/1010		240/208	2405	94 11/16	2392	94 3/16	8.6	18.8
BA2253	2250	BAL1353	1350		347	2405	94 11/16	2392	94 3/16	8.6	18.8
BA2256	2250	BAL1356	1350		600	2405	94 11/16	2392	94 3/16	8.6	18.8
---	2500	---	1500		120	2629	103 1/2	2616	103	9.4	20.7
BA2508	2500	BAL1508	1500		208	2629	103 1/2	2616	103	9.4	20.7
BA2502	2500/1875	BAL1502	1500/1125		240/208	2629	103 1/2	2616	103	9.4	20.7
BA2503	2500	BAL1503	1500		347	2629	103 1/2	2616	103	9.4	20.7
BA2506	2500	BAL1506	1500		600	2629	103 1/2	2616	103	9.4	20.7