

## Extra Duty Weatherproof Cover



The single gang extra-duty plastic weatherproof cover(SWP25005) is with a gasket, mounting screws, base and cover assembly, inserts for a variety of applications.


### Features:

- . Comply with 2014 Article 406.9(B)(1) for wet locations and extra-duty applications, and meet UL 514D standard.
- . UV stabilized polycarbonate for longtime durability.
- . Cover mounts horizontally or vertically with base.
- . Includes 2 inserts matching decorative devices, duplex receptacles, and a variety of single receptacles and toggle switches.


### Ratings:

- . Cover: UV stabilized polycarbonate(PC) plastic.
- . Certified for Type 3R.
- . Outdoor Enclosures
- . Cover cord opening: Horizontal- 2 cord outlets 0.5" wide by 0.9" high.  
Vertical- 2 cord outlets 0.5" wide by 0.9" high.
- . Gasket: PE with slits for mounting screws
- . Cord size: Fits #12AWG or lighter cord.
- . Hinge Pin: Plated steel

### Product Dimensions:



Vertical



Horizontal

