




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT P/N | WEIGHT |
|---------------------------|-------------------------------------|
| CPP48HDWBLY CPP48HDWWH | 6.15 LB/10 PCS (2788.0 g/10 PCS) |

NOTES:

1. SEE WWW.PANDUIT.COM FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
2. THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
3. PACKAGE CONTENTS:
 (1) -48 PORT STAMPING
 (6) -8 POSITION FACEPLATE (ASSEMBLED TO PANEL)
 (1) -SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
4. DIMENSIONS IN [] ARE IN METRIC.
5. CPP48HDWBLY FABRICATED COMPONENTS ARE BLACK.
 CPP48HDWWH FABRICATED COMPONENTS ARE WHITE.



CPP48HDWWH CONFIGURATION
NOTE: NO RECTANGULAR BOXES

| | |
|---|------------------------|
| PART NUMBER CPP48HDWBLY/CPP48HDWWH | |
| TITLE MINI-COM 48 PORT HIGH DENSITY MODULAR PATCH PANEL | |
| CUSTOMER DRAWING | |
| ITEM REVISION NAME M02479DA/04 | PANDUIT |
| DATASET FILE NAME M02479DA_DC81/04A | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .xxx ± .010 [.3] .xx ± .03 [.8] ANGLES ± | |
| MATERIAL: STAMPING: 18 GAGE C.R.S. FACEPLATE: ABS | |
| DRAWING NUMBER: 02479-081 | |
| DRAWN BY JSP | DATE 3-11-06 |
| CHK MJD | SCALE NONE |
| THIRD ANGLE PROJECTION | |
| SHT 1 OF 1 | |
| SIZE A | |

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|--------|-----|------|-----|---|----------|
| 04A | 3-2-22 | BJN | MDJR | MMR | UPDATED CAD MODEL TO REV 04 REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY | M09000PQ |

D10100DA/14