

Individual Spec Sheet

WTL

LED ADJUSTABLE WALL PACK

Selectable color temperature (3 000/4 000/5 000 K)

Power selectable

Integrated photocell

ORDERING INFORMATION

Order code: 70529
Model number: WTL-PS30A-Q-3C-BK-P
UPC: 069549035416
Case quantity: 8
DLC unique ID: P77YNXT4

PHYSICAL DATA

Finish: Black
Housing material: Die-cast aluminum
Lens material: Clear polycarbonate lens

PERFORMANCE DATA

Watts (W): 15/30
Volts (V AC): 120-347
Color temperature (K):¹ 3 000/4 000/5 000
Lumen output (lm):² 2 100 - 3 925
Efficacy (lm/W): 137 - 140
CRI: 70
Life L70 (h): 50 000
THD (%): ≤20
IP rating: IP65
IK rating: IK07
Dimming: 0-10 V
Power factor: ≥0.9
Photocell: Yes
Surge protection (kV): 6
Operating temp. range: -40°C to 50°C (-40°F to 122°F)

¹ Typical colour temperature range: +/- 5 %

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

LUMEN SPECIFICATION TABLE

Model number	Watts (W)	3 000 K			4 000 K			5 000 K		
		Lumen output (lm)	Efficiency (lm/W)	LED Current (mA)	Lumen output (lm)	Efficiency (lm/W)	LED Current (mA)	Lumen output (lm)	Efficiency (lm/W)	LED Current (mA)
WTL-PS30A-Q-3C-BK-P	15	1950	130	0.14	2100	140	0.14	2025	135	0.14
	30	3616	121	0.28	3925	137	0.28	3919	131	0.28

DEFAULT PROGRAMMING

70529: 30 W / 4 000K

This lighting equipment complies with Canadian standard ICES-005 for use in commercial applications. Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.




ICES 005



IK07



DIMENSIONS




A in. (cm)	7.36 (18.7)
B in. (cm)	3.62 (9.2)
C in. (cm)	6.42 (16.3)
D in. (cm)	4.21 (10.7)
E in. (cm)	1.54 (3.9)

PHOTOMETRIC DATA¹

70529 • WTL-PS30A-Q-3C-P • 15 W • 4 000 K • 2 099 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	729.5	34.8%
0-40	1 152.1	54.9%
0-60	1 835.1	87.4%
60-90	258.1	12.3%
70-100	87.4	4.2%
90-120	1.2	0.1%
0-90	2 093.3	99.7%
90-180	5.7	0.3%
0-180	2 099.0	100%


Illuminance at a distance

Center beam fc	Beam width
8.3'	13.9
16.7'	3.44
25'	1.54
33.3'	0.87
41.7'	0.55
50'	0.38

Vert. spread: 83.7°
Horiz. spread: 100.7°

70529 • WTL-PS30A-Q-3C-P • 30 W • 4 000 K • 3 923 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	1 363.4	34.8%
0-40	2 153.3	54.9%
0-60	3 430.0	87.4%
60-90	482.4	12.3%
70-100	163.3	4.2%
90-120	2.3	0.1%
0-90	3 912.4	99.7%
90-180	10.7	0.3%
0-180	3 923.1	100%

Illuminance at a distance

Center beam fc	Beam width
8.3'	26
16.7'	6.43
25'	2.87
33.3'	1.62
41.7'	1.03
50'	0.72

Vert. spread: 83.7°
Horiz. spread: 100.7°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____

Company: _____

Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions.
All products are subject to change or may be discontinued any time without notice.