

### SECTION 1: Identification

#### 1.1. Identification

Product form : Mixture  
Trade name : FIRST ALERT® EZ FIRE SPRAY™

#### 1.2. Recommended use and restrictions on use

Use of the substance/mixture : Fire extinguishing spray tool

#### 1.3. Supplier

BRK Brands, Inc. (First Alert)  
3901 Liberty Street Road  
Aurora, IL 60504  
Phone: 630-851-7330  
Fax: 630-851-8205

#### 1.4. Emergency telephone number

Emergency number : CHEMTREC: Within USA and Canada 1-800-424-9300

### SECTION 2: Hazard(s) identification

#### 2.1. Classification of the substance or mixture

##### GHS US classification

Gases under pressure Compressed gas Contains gas under pressure; may explode if heated

#### 2.2. GHS Label elements, including precautionary statements

##### GHS US labeling

Hazard pictograms (GHS US) :



Signal word (GHS US) : Warning  
Hazard statements (GHS US) : Contains gas under pressure; may explode if heated  
Precautionary statements (GHS US) : Protect from sunlight. Store in a well-ventilated place.

#### 2.3. Other hazards which do not result in classification

No additional information available

#### 2.4. Unknown acute toxicity (GHS US)

Not applicable

### SECTION 3: Composition/Information on ingredients

#### 3.1. Substances

Not applicable

#### 3.2. Mixtures

Name	Product identifier	%	GHS US classification
Carbonic acid, dipotassium salt	(CAS-No.) 584-08-7	3.6	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Irrit. 2, H319 STOT SE 3, H335

### SECTION 4: First-aid measures

#### 4.1. Description of first aid measures

First-aid measures after inhalation : If inhaled, remove to fresh air and keep at rest in a position comfortable for breathing. Administer oxygen if breathing is difficult. If breathing stops, give artificial respiration. If experiencing respiratory symptoms, call a doctor.  
First-aid measures after skin contact : Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse. Seek medical attention if irritation develops.

# FIRST ALERT® TUNDRA™

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

- |                                      |  |
|--------------------------------------|--|
| First-aid measures after eye contact | : Rinse eyes with water as a precaution. Seek medical attention if irritation develops.  |
| First-aid measures after ingestion   | : Rinse mouth. Never give anything by mouth to an unconscious person. Do NOT induce vomiting. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Seek medical attention if ill effect develops. |

### 4.2. Most important symptoms and effects (acute and delayed)

- |   |  |
|---|--|
| Potential Adverse human health effects and symptoms | : Not expected to present a significant hazard under anticipated conditions of normal use. |
|---|--|

### 4.3. Immediate medical attention and special treatment, if necessary

Treat symptomatically.

## SECTION 5: Fire-fighting measures

### 5.1. Suitable (and unsuitable) extinguishing media

- |                                |   |
|--------------------------------|---|
| Suitable extinguishing media   | : Use extinguishing media appropriate for surrounding fire. |
| Unsuitable extinguishing media | : Do not use a heavy water stream.                          |

### 5.2. Specific hazards arising from the chemical

- |                  |   |
|------------------|---|
| Fire hazard      | : Thermal decomposition can lead to the release of irritating gases and vapors. |
| Explosion hazard | : Contains gas under pressure; may explode if heated.                           |

### 5.3. Special protective equipment and precautions for fire-fighters

- |                                |   |
|--------------------------------|---|
| Firefighting instructions      | : Exercise caution when fighting any chemical fire. Prolonged exposure to fire may cause containers to rupture/explode. Use water spray or fog for cooling exposed containers. Prevent fire-fighting water from entering environment. |
| Protection during firefighting | : Do not enter fire area without proper protective equipment, including respiratory protection.   |

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

- |                  |  |
|------------------|--|
| General measures | : Evacuate unnecessary personnel. Provide adequate ventilation to minimize dust and/or vapor concentrations. Stop leak if safe to do so. |
|------------------|--|

#### 6.1.1. For non-emergency personnel

- |                      |  |
|----------------------|--|
| Protective equipment | : Wear personal protective equipment. For further information refer to section 8: "Exposure controls/personal protection". |
| Emergency procedures | : Avoid breathing dust, mist or spray.   |

#### 6.1.2. For emergency responders

- |                      |  |
|----------------------|--|
| Protective equipment | : Wear recommended personal protective equipment. For further information refer to section 8: "Exposure controls/personal protection". |
| Emergency procedures | : Avoid breathing dust, mist or spray.   |

### 6.2. Environmental precautions

Do not allow uncontrolled discharge of product into the environment. Prevent entry to sewers and public waters.

### 6.3. Methods and material for containment and cleaning up

- |                         |  |
|-------------------------|--|
| For containment         | : Soak up with inert absorbent material (for example sand, sawdust, a universal binder, silica gel).   |
| Methods for cleaning up | : Take up liquid spill into absorbent material. Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials. |
| Other information       | : Dispose of materials or solid residues at an authorized site.  |

### 6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of residues refer to section 13: "Disposal considerations". For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

- |                               |  |
|-------------------------------|--|
| Precautions for safe handling | : Wear personal protective equipment. Use only outdoors or in a well-ventilated area. Contains gas under pressure; may explode if heated. Damaged cylinders should be handled by specialists only. |
| Hygiene measures              | : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.  |

# FIRST ALERT® TUNDRA™

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Keep only in the original container in a cool well ventilated place. Keep the cylinders at vertical position, fixed to the wall or other solid structure. Keep container closed when not in use. Keep out of sunlight. Protect from freezing. Keep out of reach of children.
- Incompatible materials : Strong oxidizing agents.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### FIRST ALERT® TUNDRA™

No additional information available

#### Carbonic acid, dipotassium salt (584-08-7)

No additional information available

### 8.2. Appropriate engineering controls

- Appropriate engineering controls : Use only outdoors or in a well-ventilated area.
- Environmental exposure controls : Do not allow uncontrolled discharge of product into the environment.

### 8.3. Individual protection measures/Personal protective equipment

#### Hand protection:

Impermeable protective gloves.

#### Eye protection:

Chemical goggles or safety glasses.

#### Respiratory protection:

Not necessary under the recommended storage and handling conditions. In case of insufficient ventilation, wear suitable respiratory equipment

#### Other information:

Do not eat, drink or smoke during use.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

- Physical state : Liquid
- Appearance : Clear.
- Color : Yellow
- Odor : Characteristic slight
- Odor threshold : No data available
- pH : 10.5 – 11.5
- Melting point : No data available
- Freezing point : No data available
- Boiling point : No data available
- Flash point : Not applicable. This product is a fire extinguishing agent
- Relative evaporation rate (butyl acetate=1) : No data available
- Flammability (solid, gas) : Not applicable.
- Vapor pressure : No data available
- Relative vapor density at 20 °C : No data available
- Relative density : No data available
- Solubility : Soluble in water.
- Partition coefficient n-octanol/water (Log Pow) : No data available
- Auto-ignition temperature : Does not ignite
- Decomposition temperature : No data available
- Viscosity, kinematic : No data available
- Viscosity, dynamic : No data available
- Explosion limits : No data available

# FIRST ALERT® TUNDRA™

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

- Explosive properties : Contains gas under pressure; may explode if heated.  
Oxidizing properties : Not oxidising.

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

Protect from freezing. Keep out of direct sunlight. Keep away from heat.

### 10.5. Incompatible materials

Strong oxidizing agents.

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

- Acute toxicity (oral) : Not classified (On basis of test data)  
Acute toxicity (dermal) : Not classified (On basis of test data)  
Acute toxicity (inhalation) : Not classified (On basis of test data)

FIRST ALERT® TUNDRA™	
LD50 oral rat	> 5 ml/kg
LD50 dermal rabbit	> 2000 mg/kg
LC50 inhalation rat (Dust/Mist - mg/l/4h)	> 2.1 mg/l/4h

Carbonic acid, dipotassium salt (584-08-7)	
LD50 oral rat	1870 mg/kg

- Skin corrosion/irritation : Not classified (On basis of test data)  
pH: 10.5 – 11.5
- Serious eye damage/irritation : Not classified (On basis of test data)  
pH: 10.5 – 11.5
- Respiratory or skin sensitization : Not classified (Based on available data, the classification criteria are not met)
- Germ cell mutagenicity : Not classified (Based on available data, the classification criteria are not met)
- Carcinogenicity : Not classified (Based on available data, the classification criteria are not met)
- Reproductive toxicity : Not classified (Based on available data, the classification criteria are not met)
- STOT-single exposure : Not classified (Based on available data, the classification criteria are not met)

Carbonic acid, dipotassium salt (584-08-7)	
STOT-single exposure	May cause respiratory irritation.

- STOT-repeated exposure : Not classified (Based on available data, the classification criteria are not met)
- Aspiration hazard : Not classified (Based on available data, the classification criteria are not met)
- Viscosity, kinematic : No data available
- Potential Adverse human health effects and symptoms : Not expected to present a significant hazard under anticipated conditions of normal use.
- Other information : Likely routes of exposure: ingestion, inhalation, skin and eye.

## SECTION 12: Ecological information

### 12.1. Toxicity

- Ecology - general : The product has not been tested.

# FIRST ALERT® TUNDRA™

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### Carbonic acid, dipotassium salt (584-08-7)

EC50 Daphnia 1

630 mg/l (Exposure time: 48 h - Species: Ceriodaphnia dubia)

#### 12.2. Persistence and degradability

No additional information available

#### 12.3. Bioaccumulative potential

No additional information available

#### 12.4. Mobility in soil

No additional information available

#### 12.5. Other adverse effects

Effect on the ozone layer : No additional information available  
Other information : Do not allow uncontrolled discharge of product into the environment.

### SECTION 13: Disposal considerations

#### 13.1. Disposal methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.  
Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.

### SECTION 14: Transport information

#### Department of Transportation (DOT)

In accordance with DOT

Transport document description : UN1950 Aerosols, 2.2  
UN-No.(DOT) : UN1950  
Proper Shipping Name (DOT) : Aerosols  
Class (DOT) : 2.2 - Class 2.2 - Non-flammable compressed gas 49 CFR 173.115  
Hazard labels (DOT) : 2.2 - Non-flammable gas



#### Transportation of Dangerous Goods

Transport document description : UN1950 AEROSOLS, 2.2  
UN-No. (TDG) : UN1950  
Proper Shipping Name (Transportation of Dangerous Goods) : AEROSOLS  
TDG Primary Hazard Classes : 2.2 - Class 2.2 - Non-Flammable, Non-Toxic Gas

#### Transport by sea

Transport document description (IMDG) : UN 1950 AEROSOLS, 2.2  
UN-No. (IMDG) : 1950  
Proper Shipping Name (IMDG) : AEROSOLS  
Class (IMDG) : 2 - Gases

#### Air transport

Transport document description (IATA) : UN 1950 Aerosols, non-flammable, 2.2  
UN-No. (IATA) : 1950  
Proper Shipping Name (IATA) : Aerosols, non-flammable  
Class (IATA) : 2

# FIRST ALERT® TUNDRA™

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### SECTION 15: Regulatory information

#### 15.1. US Federal regulations

All components of this product are listed, or excluded from listing, on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

This product or mixture is not known to contain a toxic chemical or chemicals in excess of the applicable de minimis concentration as specified in 40 CFR §372.38(a) subject to the reporting requirements of section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 and 40 CFR Part 372.

#### 15.2. International regulations

##### CANADA

###### Carbonic acid, dipotassium salt (584-08-7)

Listed on the Canadian DSL (Domestic Substances List)

##### EU-Regulations

###### Carbonic acid, dipotassium salt (584-08-7)

Listed on the EEC inventory EINECS (European Inventory of Existing Commercial Chemical Substances)

##### National regulations

###### Carbonic acid, dipotassium salt (584-08-7)

Listed on the AICS (Australian Inventory of Chemical Substances)  
Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China)  
Listed on the Japanese ENCS (Existing & New Chemical Substances) inventory  
Listed on the Japanese ISHL (Industrial Safety and Health Law)  
Listed on KECL/KECI (Korean Existing Chemicals Inventory)  
Listed on NZIoC (New Zealand Inventory of Chemicals)  
Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances)  
Listed on INSQ (Mexican National Inventory of Chemical Substances)  
Listed on the TCSI (Taiwan Chemical Substance Inventory)

#### 15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

### SECTION 16: Other information

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Revision date : 18 June 2020  
Data sources : Manufacturer Information.  
Other information : None.

SDS US (GHS HazCom 2012)

*This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.*