SMOKE ALARM PHOTOELECTRIC

Model 7010BA CAT. 7016BTCA









OptiPath 360 Technology

PHOTOELECTRIC

Photoelectric technology is generally more sensitive at detecting large particles, which tend to be produced in greater amounts by smoldering fires.

LATCHING ALARM INDICATOR

Remembers which unit initiated an alarm.

OPTIPATH 360 TECHNOLOGY™

Provides 360 degrees of direct access to the smoke sensing chamber.

SILENCE FEATURE

Silences nuisance alarms.

TWO LOCKING FEATURES

Pins are provided to lock battery drawer and/or alarm to base. Perfect for apartment, dormitory or hotel applications.

END OF LIFE SIGNAL

Provides audible notice when alarm needs to be replaced after 10 years.









THE PROFESSIONAL STANDARD

120V AC, 60Hz Wire-in with 9V Battery Backup

Description:


BRK Model 7010BA (Cat. 7016BTCA) is a wire-in, 120V AC 60Hz single and/or multiple station photoelectric smoke alarm specifically designed for residential and institutional applications including sleeping rooms of hospitals, hotels, motels, dormitories and other multi-family dwellings as defined in standard NFPA 101. Model 7010BA complies with ULC S531, NFPA 72, HUD, FHA and other agencies that model their codes after the above agencies. Alarms are interconnectable with up to 18 devices, of which 12 can be smoke alarms.

BRK 7010BA features a photoelectric smoke sensing chamber, an 85dB horn, a 9V battery back-up and a "silence" feature. Optipath 360 technology provides 360 degrees of direct access to the smoke sensing chamber. Alarm Latch: Easily identifies initiating alarm even after alarm condition has subsided. The "Perfect Mount" system features a gasketless base and a mounting bracket that keeps the alarm secure over a wide rotation range to allow for true alignment. This will allow fine-tuning on the positioning to compensate for out of aligned wall studs and to keep the wording level when wall mounting. Battery installation and removal can occur while the unit is mounted to the ceiling or wall via the side load battery compartment. Other Contractor Preferred features include a dust cover to keep alarm clean during construction, keyhole slots in the mounting bracket eliminate the need to remove the electrical box screws for installation. Two locking features are provided to prevent battery theft and/or theft of the unit. Connection to AC power is made with a "Quick-Connect" wiring harness. Installation is quick, easy and cost effective.




Model 7010BA CAT. 7016BTCA









ARCHITECTURAL AND ENGINEERING SPECS


The smoke alarm shall be a BRK Model 7010BA (Cat. 7016BTCA) and shall provide at a minimum the following features and functions:

- 1. A photoelectric smoke sensing chamber.
- A fully screened sensing chamber to resist entry of small insects thereby reducing the probability of unwanted alarms.
- Powered by 120V AC, 60Hz and have a monitored 9V battery backup and a solid state piezo horn rated at 85dB at 10 ft.
- 4. A visual LED power-on indicator to confirm unit is receiving power or is in alarm.
- A full function test button. The test button should check all alarm functions by stimulating the chamber to simulate a smoke condition, causing the unit to alarm.
- Latching & silence features: Alarm Latch to easily identify initiating alarm after alarm condition has subsided. Silence feature - Temporarily silence unwanted nuisance alarms.
- Two Locking features tamper resistant locking pins that lock battery drawer and/or alarm to mounting bracket.
- The unit shall be capable of operating between 40°F (4°C) and 100°F (38°C) and relative humidity between 10% and 95%.
- The unit shall have a gasketless base for easy installation and be capable of keeping alarm secure over a wide rotation range to allow for true alarm alignment.
- 10. The unit shall have a plug in connector and be capable of interconnection of up to 18 alarms, 12 of which can be smoke alarms.
- 11. The unit shall at a minimum meet the requirements of ULC S531, NFPA 72, NFPA 101, and ICC.
- 12. The unit shall have an "End of Life" signal.

INSTALLATION OF ALARM

Installation of this smoke alarm must conform to all local electrical codes and Article 760 of the National Electrical Code (NFPA 70) and NFPA 72. Interconnected units must meet the following requirements: Total length of wire interconnecting units should be less than 1000 feet, be #18 gauge or larger and be rated at least 300V. It is recommended that all units be on the same fuse or circuit breaker. If local codes do not permit, be sure the neutral wire is common to both phases.

THE PARTS OF THIS ALARM



- 1. Mounting bracket
 2. Mounting Slots
 3. Locking Pins
 4. Hot (Black) AC Wire
 5. Neutral (White) AC Wire
 6. Interconnect (Orange) Wire
 7. Pull out Battery Drawer
 8. Quick-Connect Plug
- e Wire r A 5 4 3 2

678

- A. Unswitched 120VAC 60 Hz source
- To additional units; Maximum = 18 total (Maximum 12 Smoke Alarms)
- Smoke Alarm
 Ceiling or Wall
- Junction Box
- Power Connector
- Neutral Wire (White)
 Interconnect Wire (Orange)
- 4. Wire Nut
- 8. Hot Wire (Black)

TECHNICAL SPECS

Alarm Dimensions:	5.0" Dia. x 2.1" H
Weight:	8.4 oz
Operating Voltage:	120V AC 60Hz w/ 9V battery backup
Temperature Range:	40°F (4°C) to 100°F (38°C)
Humidity Range:	10% to 95% relative humidity (RH)
Audio Alarm:	85dB at 10 feet
Test/Silence:	Electronically simulates smoke condition, causing the unit to alarm. Press and hold test/silence button.
Alarm Reset:	Unit will remain in latch mode until manually reset
Interconnections:	Up to 18 units of First Alert or BRK Smoke, CO and Heat Alarms. Maximum of 12 smoke alarms. See user's manual for details.
Smoke Sensor:	Photoelectric
Indicator Lights/Sounds: AC Power: DC Power: Local Alarm: Latching Alarm: Remote Alarm: End of Life:	Constant Green LED Intermittent Red LED Red LED flashes rapidly Green LED flashes Audio alarm and Red LED out Horn sounds 5 chirps; pattern repeats once/minute
Listing:	Certified to ULC STD S531

SHIPPING SPECS

Individual Carton Dimensions Weight:	5.1" L x 2.4" W x 5.1" H 0.6 lbs.
Cube:	0.04 ft ³
UPC:	0 29054 01043 8
Master Carton Dimensions	10.6" L x 7.9" W x 10.9" H
Master Pack:	12
Weight:	8.2 lbs.
Cube:	0.5 ft ³
I2of5:	200 29054 01043 2
Pallet Information	
Cases per Layer:	22
Number of Layers:	4
Cases per Pallet:	88
Units per Pallet:	1056
Cube:	53.9 ft ³
Weight:	748 lbs.



© 2021 BRK Brands, Inc. All rights reserved. Distributed by BRK Brands, Inc., Aurora, Illinois 60504. BRK Brands, Inc. is a subsidiary of Newell Brands Inc. (NASDAQ: NWL).