


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	MATERIAL	"A" HEIGHT +/- .06	IMPRINT AREA "B" +/- .06	VERTICAL REPEAT "C" +/- .06	LABELS PER ROW	STANDARD PKG. QTY.
S100X075VATY	GMV17	0.75 [19.0]	0.25 [6.35]	1.00 [25.4]	4	5000
S100X125VATY	GMV17	1.25 [31.8]	0.38 [9.65]	1.50 [38.1]		
S100X150VATY	GMV17 OR GMV19	1.50 [38.1]	0.50 [12.7]	1.80 [45.7]		
S100X150VATY-CR	GMV17					
S100X160VATY	GMV17 OR GMV19	1.60 [40.6]	0.80 [20.3]	1.85 [45.9]		1000
S100X225VATY	GMV17 OR GMV18	2.25 [57.2]	0.75 [19.1]	2.50 [63.5]		5000
S100X225VATY-CR	GMV17					
S100X250VATY	GMV17 OR GMV18	2.50 [63.5]	1.00 [25.4]	2.75 [69.8] 4.25 [107.95]		2500
S100X400VATY	GMV17 OR GMV18	4.00 [101.6]				
S100X650VATY	GMV17 OR GMV18	6.50 [165.1]	1.50 [38.1] +/- .062	6.75 [171.4]		1000

NOTE:
1. MILLIMETERS ARE IN [].

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
16B	8/1/2024	RVU	RYCL	MSAD	B. REMOVED S100X***TAT FROM TITLE. A. PN's: S100X150VATY AND S100X160VATY, REPLACED FROM GMV18 TO GMV19.	GAECN07205
16A	9/26/2022	RVU	JEFP	MSAD	REMOVED S100X250TAT AND S100X400TAT FROM TABLE. S100X150VATY, AND S100X225VATY -GMV17 OR GMV18 WAS GMV18. S100X160VATY, S100X250VATY, S100X400VATY, AND S100X650VATY-GMV17 OR GMV18 WAS GMV17.	GAECN06240

TITLE OPTIMUM SELF-LAM. S100X***VATY THERMAL TRANSFER PRINTABLE LABELS		CUSTOMER DRAWING	
ITEM REVISION NAME 100472BU/16		PANDUIT	
DATASET FILE NAME 100472BU_DC/16B C10196 CUST DWG		MATERIAL: SEE TABLE	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .025 [.635] .xx ± .06 [1.52] ANGLES ±		DRAWING NUMBER: C10196	
THIRD ANGLE PROJECTION	DRAWN BY RVU	DATE 9/1/06	CHK JHAC
SCALE NTS	SHT 1 OF 1		SIZE A

D10100DA/20