

DIAMOND WET CORE BIT EXTENSIONS

Size	Thread	Part No.
1"	5/8"-11	48-17-4010
1-1/4"	5/8"-11	48-17-4012
1-1/2"	5/8"-11	48-17-4015
2"	1-1/4"-7	48-17-4020
2-1/2"	1-1/4"-7	48-17-4025
3"	1-1/4"-7	48-17-4030

Size	Thread	Part No.
3-1/2"	1-1/4"-7	48-17-4035
4"	1-1/4"-7	48-17-4040
4-1/4"	1-1/4"-7	48-17-4042
4-1/2"	1-1/4"-7	48-17-4045
5"	1-1/4"-7	48-17-4050

DIAMOND ULTRA DRY CORE BITS

OVERVIEW

MILWAUKEE® Diamond Ultra Dry Core Bits are engineered with thin kerf segments to provide the fastest drilling in concrete, brick and block applications. These Diamond Ultra Dry Core Bits deliver up to 20% longer run-time versus other MILWAUKEE® dry core bits. The Diamond Ultra Dry Core Bits are specifically designed for use with the MX FUEL™ Core Drill and corded core drills. The Ultra Dry Core Bits feature a 13" drilling depth and 1-1/4"-7 thread connection for easy no-adaptor use in the MX FUEL™ Core Drill.

FEATURES

- Fastest drilling compared to other MILWAUKEE® dry core bits
- Maximum Run-Time
- Ideal for concrete, brick and block

DIAMOND ULTRA DRY CORE BITS

Size	Thread	Part No.
1-1/4"	1-1/4"-7	48-17-0112
2"	1-1/4"-7	48-17-0120
2-1/2"	1-1/4"-7	48-17-0125
3"	1-1/4"-7	48-17-0130

Size	Thread	Part No.
3-1/2"	1-1/4"-7	48-17-0135
4"	1-1/4"-7	48-17-0140
5"	1-1/4"-7	48-17-0150
6"	1-1/4"-7	48-17-0160



DIAMOND DRY CORE BITS

OVERVIEW

MILWAUKEE® Diamond Dry Core Bits are designed to the highest standards, using only quality diamonds. Available in sizes 1"–6", Diamond Dry Core Bits are ideal for drilling brick and block with no reinforcement. The large slots facilitate cooling of the bit as well as extracting the cores. The thinner wall provides increased drilling speed. This bit is 10" in length and contains a 5/8–11 thread.

FEATURES

- For use in masonry, brick and block with no reinforcement
- 10" Drilling Depth
- Designed to be used dry



DIAMOND DRY CORE BITS

Size	Thread	Part No.
1"	5/8"-11	48-17-0010
1-1/2"	5/8"-11	48-17-0015
2"	5/8"-11	48-17-0020
2-1/2"	5/8"-11	48-17-0025
3"	5/8"-11	48-17-0030

Size	Thread	Part No.
3-1/2"	5/8"-11	48-17-0035
4"	5/8"-11	48-17-0040
4-1/2"	5/8"-11	48-17-0045
5"	5/8"-11	48-17-0050
6"	5/8"-11	48-17-0060

DIAMOND CORE BIT ACCESSORIES

DIAMOND CORE BIT ADAPTERS

Description	Thread	Part No.
5/8"-11 6-Slot Core Bit Adapter	5/8"-11	48-17-6002
1-1/4"-7 6-Slot Core Bit Adapter	1-1/4"-7	48-17-6004
Copper Spindle Spacer	-	45-88-8565
1-1/4" Female – 5/8" Male Core Bit Adapter	1-1/4"-7	48-17-6006
5/8" Female – 1-1/4" Male Core Bit Adapter	5/8"-11	48-17-6008

DIAMOND CORE BIT EXTENSIONS

Description	Thread	Part No.
5/8"-11 x 6" Core Bit Extension	5/8"-11	48-17-6010
5/8"-11 x 12" Core Bit Extension	5/8"-11	48-17-6012
1-1/4"-7 x 6" Core Bit Extension	1-1/4"-7	48-17-6014
1-1/4"-7 x 12" Core Bit Extension	1-1/4"-7	48-17-6016



DIAMOND CUTTING & CORING

DIAMOND CUTTING & CORING